

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1296882

Luminaire Tested: P3AS13R35W2N902765DE010 E3DLD1LI_4000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1296882
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-18)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R35W2N902765DE010 E3DLD1LI_4000K
Description: 3in Adjustable Tunable White LED luminaire with, R35 optic, 4000K CCT AND, 90CRI ,
E3DLD1LI TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 628.0 lumens
Efficiency: N/A
Efficacy: 51.1 lumens/watt
Spacing Criteria (0/90/45): 0.8 / 0.8 / 0.87
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 12.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1296882
CATALOG NUMBER: P3AS13R35W2N902765DE010 E3DLD1LI_4000K

Luminous Intensity Polar Plot





TEST NUMBER: P1296882

CATALOG NUMBER: P3AS13R35W2N902765DE010 E3DLD1LI_4000K

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10° | 59.4 | 9.5 |
| 10°-20° | 144.7 | 23.0 |
| 20°-30° | 165.8 | 26.4 |
| 30°-40° | 135.3 | 21.5 |
| 40°-50° | 68.2 | 10.9 |
| 50°-60° | 25.3 | 4.0 |
| 60°-70° | 17.0 | 2.7 |
| 70°-80° | 9.4 | 1.5 |
| 80°-90° | 2.9 | 0.5 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-30° | 369.9 | 58.9 |
| 0°-40° | 505.2 | 80.4 |
| 0°-60° | 598.8 | 95.3 |
| 0°-90° | 628.0 | 100.0 |
| 90°-120° | 0.0 | 0.0 |
| 90°-150° | 0.0 | 0.0 |
| 90°-180° | 0.0 | 0.0 |
| 0°-180° | 628.0 | 100.0 |

CANDELA DISTRIBUTION:

| | 0° | Flux |
|-----|-----|------|
| 0° | 654 | |
| 5° | 638 | 59 |
| 15° | 520 | 145 |
| 25° | 362 | 166 |
| 35° | 218 | 135 |
| 45° | 86 | 68 |
| 55° | 26 | 25 |
| 65° | 17 | 17 |
| 75° | 8 | 9 |
| 85° | 2 | 3 |
| 90° | 0 | |



TEST NUMBER: P1296882

CATALOG NUMBER: P3AS13R35W2N902765DE010 E3DLD1LI_4000K

CANDELA DISTRIBUTION (FULL):

| 0° | |
|-------|-------|
| 0° | 654.2 |
| 1° | 653.4 |
| 2° | 651.9 |
| 3° | 648.8 |
| 4° | 644.1 |
| 5° | 637.9 |
| 6° | 630.1 |
| 7° | 622.4 |
| 8° | 612.3 |
| 9° | 602.2 |
| 10° | 590.6 |
| 11° | 578.2 |
| 12° | 565.0 |
| 13° | 550.2 |
| 14° | 534.7 |
| 15° | 519.9 |
| 17.5° | 480.4 |
| 20° | 440.0 |
| 22.5° | 398.9 |
| 25° | 361.6 |
| 27.5° | 325.2 |
| 30° | 289.5 |
| 32.5° | 253.8 |
| 35° | 218.1 |
| 37.5° | 182.4 |
| 40° | 147.4 |
| 42.5° | 114.9 |
| 45° | 86.1 |
| 47.5° | 62.1 |
| 50° | 42.7 |
| 52.5° | 31.0 |
| 55° | 26.4 |
| 57.5° | 24.1 |
| 60° | 21.7 |
| 62.5° | 19.4 |
| 65° | 17.1 |
| 67.5° | 14.7 |
| 70° | 13.2 |
| 72.5° | 10.9 |
| 75° | 8.5 |
| 77.5° | 7.0 |
| 80° | 5.4 |
| 82.5° | 3.9 |
| 85° | 2.3 |
| 87.5° | 1.6 |



TEST NUMBER: P1296882
CATALOG NUMBER: P3AS13R35W2N902765DE010 E3DLD1LI_4000K

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)