

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1296883

Luminaire Tested: P3AS13R35W2N902765DE010 E3DLD1LI\_5000K

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1296883  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-18)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS13R35W2N902765DE010 E3DLD1LI\_5000K  
Description: 3in Adjustable Tunable White LED luminaire with, R35 optic, 5000K CCT AND, 90CRI ,  
E3DLD1LI TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 624.0 lumens  
Efficiency: N/A  
Efficacy: 50.7 lumens/watt  
Spacing Criteria (0/90/45): 0.8 / 0.8 / 0.87  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 12.3  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1296883  
CATALOG NUMBER: P3AS13R35W2N902765DE010 E3DLD1LI\_5000K

### Luminous Intensity Polar Plot





TEST NUMBER: P1296883

CATALOG NUMBER: P3AS13R35W2N902765DE010 E3DLD1LI\_5000K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	112	109	106	104	110	107	104	102	103	101	99	99	98	96	96	94	93	91			
2	106	100	96	92	104	98	94	91	95	92	89	92	89	87	89	87	85	83			
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76			
4	94	85	79	74	92	84	78	74	82	77	73	80	75	72	78	74	71	69			
5	89	79	73	68	87	78	72	67	76	71	67	75	70	66	73	69	66	64			
6	84	74	67	62	82	73	67	62	71	66	61	70	65	61	68	64	61	59			
7	79	69	62	57	78	68	62	57	67	61	57	65	60	57	64	60	56	55			
8	75	64	58	53	74	64	57	53	63	57	53	62	56	53	61	56	52	51			
9	71	60	54	50	70	60	54	50	59	53	49	58	53	49	57	52	49	48			
10	67	57	51	46	66	56	50	46	56	50	46	55	50	46	54	49	46	45			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	142532
5°	139511
10°	130659
15°	117276
20°	102022
25°	86932
30°	72821
35°	58009
40°	41936
45°	26545
50°	14464
55°	10016
60°	9473
65°	8821
70°	8399
75°	7202
80°	6819
85°	5787

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 26545 cd/sqm



TEST NUMBER: P1296883

CATALOG NUMBER: P3AS13R35W2N902765DE010 E3DLD1LI\_5000K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	59.0	9.5
10°-20°	143.8	23.0
20°-30°	164.7	26.4
30°-40°	134.4	21.5
40°-50°	67.8	10.9
50°-60°	25.2	4.0
60°-70°	16.9	2.7
70°-80°	9.3	1.5
80°-90°	2.8	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	367.5	58.9
0°-40°	501.9	80.4
0°-60°	594.9	95.3
0°-90°	624.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	624.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	650	
5°	634	59
15°	517	144
25°	359	165
35°	217	134
45°	86	68
55°	26	25
65°	17	17
75°	8	9
85°	2	3
90°	0	



TEST NUMBER: P1296883  
CATALOG NUMBER: P3AS13R35W2N902765DE010 E3DLD1LI\_5000K

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	650.0
1°	649.3
2°	647.7
3°	644.6
4°	640.0
5°	633.8
6°	626.1
7°	618.4
8°	608.4
9°	598.4
10°	586.8
11°	574.5
12°	561.4
13°	546.7
14°	531.3
15°	516.6
17.5°	477.3
20°	437.2
22.5°	396.3
25°	359.3
27.5°	323.1
30°	287.6
32.5°	252.1
35°	216.7
37.5°	181.2
40°	146.5
42.5°	114.1
45°	85.6
47.5°	61.7
50°	42.4
52.5°	30.8
55°	26.2
57.5°	23.9
60°	21.6
62.5°	19.3
65°	17.0
67.5°	14.7
70°	13.1
72.5°	10.8
75°	8.5
77.5°	6.9
80°	5.4
82.5°	3.9
85°	2.3
87.5°	1.5



TEST NUMBER: P1296883  
CATALOG NUMBER: P3AS13R35W2N902765DE010 E3DLD1LI\_5000K

CANDELA DISTRIBUTION (continued):

0°  
90° | 0.0

(END OF REPORT)