

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1299108

Luminaire Tested: P3AS17R15W2N902750DE010 E3CB1MMS_3000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1299108
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-4)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R15W2N902750DE010 E3CB1MMS_3000K
Description: 3in Adjustable Tunable White LED luminaire with, R15 optic, 3000K CCT AND, 90CRI ,
E3CB1MMS TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1510.0 lumens
Efficiency: N/A
Efficacy: 77.8 lumens/watt
Spacing Criteria (0/90/45): 0.3 / 0.3 / 0.29
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 19.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1299108
CATALOG NUMBER: P3AS17R15W2N902750DE010 E3CB1MMS_3000K

Luminous Intensity Polar Plot





TEST NUMBER: P1299108

CATALOG NUMBER: P3AS17R15W2N902750DE010 E3CB1MMS_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

| | | | | | | | | | | | | | | | | | | | | | |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|
| RF | 20 | | | | 20 | | | | 20 | | | | 20 | | | | 20 | | | | |
| RC | 80 | | | | 70 | | | | 50 | | | | 30 | | | | 10 | | | 0 | |
| RW | 70 | 50 | 30 | 10 | 70 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 0 |
| RCR | | | | | | | | | | | | | | | | | | | | | |
| 0 | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 102 | 102 | 102 | 100 |
| 1 | 116 | 114 | 112 | 111 | 113 | 112 | 110 | 109 | 108 | 107 | 106 | 104 | 103 | 103 | 101 | 100 | 100 | 100 | 100 | 100 | 98 |
| 2 | 113 | 110 | 107 | 105 | 111 | 108 | 106 | 104 | 105 | 103 | 101 | 102 | 101 | 99 | 99 | 98 | 97 | 97 | 98 | 97 | 96 |
| 3 | 110 | 106 | 103 | 100 | 108 | 105 | 102 | 100 | 102 | 100 | 98 | 100 | 98 | 97 | 98 | 97 | 95 | 98 | 97 | 95 | 94 |
| 4 | 107 | 103 | 100 | 97 | 106 | 102 | 99 | 97 | 100 | 97 | 95 | 98 | 96 | 94 | 97 | 95 | 93 | 97 | 95 | 93 | 92 |
| 5 | 105 | 100 | 97 | 94 | 104 | 99 | 96 | 94 | 98 | 95 | 93 | 96 | 94 | 92 | 95 | 93 | 92 | 95 | 93 | 92 | 91 |
| 6 | 103 | 98 | 94 | 92 | 102 | 97 | 94 | 92 | 96 | 93 | 91 | 95 | 92 | 91 | 94 | 92 | 90 | 94 | 92 | 90 | 89 |
| 7 | 101 | 96 | 92 | 90 | 100 | 95 | 92 | 90 | 94 | 91 | 89 | 93 | 91 | 89 | 92 | 90 | 89 | 92 | 90 | 89 | 88 |
| 8 | 99 | 94 | 90 | 88 | 98 | 93 | 90 | 88 | 92 | 90 | 88 | 92 | 89 | 87 | 91 | 89 | 87 | 91 | 89 | 87 | 86 |
| 9 | 97 | 92 | 89 | 87 | 97 | 92 | 89 | 86 | 91 | 88 | 86 | 90 | 88 | 86 | 90 | 87 | 86 | 90 | 87 | 86 | 85 |
| 10 | 96 | 90 | 87 | 85 | 95 | 90 | 87 | 85 | 89 | 87 | 85 | 89 | 86 | 85 | 88 | 86 | 85 | 88 | 86 | 85 | 84 |

AVERAGE LUMINANCE (cd/sqm):

| | |
|-----|---------|
| | 0° |
| 0° | 2935072 |
| 5° | 2459888 |
| 10° | 1158696 |
| 15° | 349332 |
| 20° | 129255 |
| 25° | 50253 |
| 30° | 18737 |
| 35° | 5755 |
| 40° | 2061 |
| 45° | 1116 |
| 50° | 819 |
| 55° | 918 |
| 60° | 1053 |
| 65° | 623 |
| 70° | 769 |
| 75° | 1017 |
| 80° | 0 |
| 85° | 0 |

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 1116 cd/sqm



TEST NUMBER: P1299108

CATALOG NUMBER: P3AS17R15W2N902750DE010 E3CB1MMS_3000K

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10° | 864.0 | 57.2 |
| 10°-20° | 513.5 | 34.0 |
| 20°-30° | 107.9 | 7.1 |
| 30°-40° | 17.4 | 1.2 |
| 40°-50° | 3.0 | 0.2 |
| 50°-60° | 2.2 | 0.1 |
| 60°-70° | 1.3 | 0.1 |
| 70°-80° | 0.8 | 0.1 |
| 80°-90° | 0.0 | 0.0 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-30° | 1485.4 | 98.4 |
| 0°-40° | 1502.8 | 99.5 |
| 0°-60° | 1507.9 | 99.9 |
| 0°-90° | 1510.0 | 100.0 |
| 90°-120° | 0.0 | 0.0 |
| 90°-150° | 0.0 | 0.0 |
| 90°-180° | 0.0 | 0.0 |
| 0°-180° | 1510.0 | 100.0 |

CANDELA DISTRIBUTION:

| | 0° | Flux |
|-----|-------|------|
| 0° | 13385 | |
| 5° | 11175 | 864 |
| 15° | 1539 | 514 |
| 25° | 208 | 108 |
| 35° | 22 | 17 |
| 45° | 4 | 3 |
| 55° | 2 | 2 |
| 65° | 1 | 1 |
| 75° | 1 | 1 |
| 85° | 0 | 0 |
| 90° | 0 | |



TEST NUMBER: P1299108
CATALOG NUMBER: P3AS17R15W2N902750DE010 E3CB1MMS_3000K

CANDELA DISTRIBUTION (FULL):

| | 0° |
|-------|---------|
| 0° | 13385.0 |
| 1° | 13343.2 |
| 2° | 13130.7 |
| 3° | 12705.8 |
| 4° | 12082.6 |
| 5° | 11175.3 |
| 6° | 10109.2 |
| 7° | 8890.3 |
| 8° | 7726.4 |
| 9° | 6408.4 |
| 10° | 5203.8 |
| 12.5° | 2807.8 |
| 15° | 1538.8 |
| 17.5° | 901.3 |
| 20° | 553.9 |
| 22.5° | 339.0 |
| 25° | 207.7 |
| 27.5° | 125.4 |
| 30° | 74.0 |
| 32.5° | 41.8 |
| 35° | 21.5 |
| 37.5° | 11.9 |
| 40° | 7.2 |
| 42.5° | 4.8 |
| 45° | 3.6 |
| 47.5° | 2.4 |
| 50° | 2.4 |
| 52.5° | 2.4 |
| 55° | 2.4 |
| 57.5° | 2.4 |
| 60° | 2.4 |
| 62.5° | 1.2 |
| 65° | 1.2 |
| 67.5° | 1.2 |
| 70° | 1.2 |
| 72.5° | 1.2 |
| 75° | 1.2 |
| 77.5° | 0.0 |
| 80° | 0.0 |
| 82.5° | 0.0 |
| 85° | 0.0 |
| 87.5° | 0.0 |
| 90° | 0.0 |

(END OF REPORT)