

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1296892

Luminaire Tested: P3AS13R35W2N902765DE010 E3DLD1WH\_3000K

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1296892  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-18)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS13R35W2N902765DE010 E3DLD1WH\_3000K  
Description: 3in Adjustable Tunable White LED luminaire with, R35 optic, 3000K CCT AND, 90CRI ,  
E3DLD1WH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 618.0 lumens  
Efficiency: N/A  
Efficacy: 50.2 lumens/watt  
Spacing Criteria (0/90/45): 0.8 / 0.8 / 0.87  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 12.3  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1296892  
CATALOG NUMBER: P3AS13R35W2N902765DE010 E3DLD1WH\_3000K

### Luminous Intensity Polar Plot







TEST NUMBER: P1296892

CATALOG NUMBER: P3AS13R35W2N902765DE010 E3DLD1WH\_3000K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	58.4	9.5
10°-20°	142.4	23.0
20°-30°	163.2	26.4
30°-40°	133.2	21.5
40°-50°	67.1	10.9
50°-60°	24.9	4.0
60°-70°	16.7	2.7
70°-80°	9.3	1.5
80°-90°	2.8	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	364.0	58.9
0°-40°	497.1	80.4
0°-60°	589.2	95.3
0°-90°	618.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	618.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	644	
5°	628	58
15°	512	142
25°	356	163
35°	215	133
45°	85	67
55°	26	25
65°	17	17
75°	8	9
85°	2	3
90°	0	



TEST NUMBER: P1296892  
CATALOG NUMBER: P3AS13R35W2N902765DE010 E3DLD1WH\_3000K

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	643.8
1°	643.0
2°	641.5
3°	638.4
4°	633.9
5°	627.7
6°	620.1
7°	612.5
8°	602.5
9°	592.6
10°	581.2
11°	568.9
12°	556.0
13°	541.5
14°	526.2
15°	511.7
17.5°	472.7
20°	433.0
22.5°	392.5
25°	355.9
27.5°	320.0
30°	284.9
32.5°	249.7
35°	214.6
37.5°	179.5
40°	145.1
42.5°	113.0
45°	84.8
47.5°	61.1
50°	42.0
52.5°	30.5
55°	26.0
57.5°	23.7
60°	21.4
62.5°	19.1
65°	16.8
67.5°	14.5
70°	13.0
72.5°	10.7
75°	8.4
77.5°	6.9
80°	5.3
82.5°	3.8
85°	2.3
87.5°	1.5



TEST NUMBER: P1296892  
CATALOG NUMBER: P3AS13R35W2N902765DE010 E3DLD1WH\_3000K

CANDELA DISTRIBUTION (continued):

0°  
90° | 0.0

(END OF REPORT)