

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1296906

Luminaire Tested: P3AS13R35W2N902765DE010 E3DLP1GPH_4000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1296906
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-17)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R35W2N902765DE010 E3DLP1GPH_4000K
Description: 3in Adjustable Tunable White LED luminaire with, R35 optic, 4000K CCT AND, 90CRI ,
E3DLP1GPH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 247.0 lumens
Efficiency: N/A
Efficacy: 20.1 lumens/watt
Spacing Criteria (0/90/45): 0.69 / 0.69 / 0.72
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 12.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1296906
CATALOG NUMBER: P3AS13R35W2N902765DE010 E3DLP1GPH_4000K

Luminous Intensity Polar Plot





TEST NUMBER: P1296906
 CATALOG NUMBER: P3AS13R35W2N902765DE010 E3DLP1GPH_4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93	93	93	93
2	107	102	98	94	105	100	97	93	97	94	91	94	92	89	91	89	87	86	86	86	86
3	102	95	90	86	100	94	89	85	91	87	84	89	85	82	86	84	81	80	80	80	80
4	97	89	83	79	95	88	82	78	86	81	77	84	80	77	82	78	76	74	74	74	74
5	92	83	77	73	90	82	77	73	81	76	72	79	75	71	77	74	71	69	69	69	69
6	87	78	72	68	86	77	72	68	76	71	67	75	70	67	73	69	66	65	65	65	65
7	83	74	68	63	82	73	67	63	72	67	63	71	66	63	69	65	62	61	61	61	61
8	79	70	64	60	78	69	63	59	68	63	59	67	62	59	66	62	59	57	57	57	57
9	76	66	60	56	75	66	60	56	65	59	56	64	59	56	63	59	56	54	54	54	54
10	72	63	57	53	71	62	57	53	61	56	53	61	56	53	60	56	53	51	51	51	51

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	79402
5°	77438
10°	70785
15°	60091
20°	47557
25°	35978
30°	26181
35°	17721
40°	10878
45°	6264
50°	3753
55°	3058
60°	2675
65°	2387
70°	1923
75°	1949
80°	1894
85°	2013

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 6264 cd/sqm



TEST NUMBER: P1296906

CATALOG NUMBER: P3AS13R35W2N902765DE010 E3DLP1GPH_4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	32.5	13.2
10°-20°	73.0	29.5
20°-30°	68.3	27.6
30°-40°	41.8	16.9
40°-50°	16.5	6.7
50°-60°	7.2	2.9
60°-70°	4.5	1.8
70°-80°	2.4	1.0
80°-90°	0.8	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	173.7	70.3
0°-40°	215.5	87.3
0°-60°	239.3	96.9
0°-90°	247.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	247.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	362	
5°	352	33
15°	265	73
25°	149	68
35°	66	42
45°	20	16
55°	8	7
65°	5	5
75°	2	2
85°	1	1
90°	0	



TEST NUMBER: P1296906
CATALOG NUMBER: P3AS13R35W2N902765DE010 E3DLP1GPH_4000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	362.1
1°	362.4
2°	361.3
3°	359.0
4°	355.6
5°	351.8
6°	346.8
7°	341.1
8°	334.3
9°	326.7
10°	317.9
11°	308.8
12°	298.9
13°	288.3
14°	276.5
15°	264.7
17.5°	234.3
20°	203.8
22.5°	174.6
25°	148.7
27.5°	124.7
30°	103.4
32.5°	83.7
35°	66.2
37.5°	50.6
40°	38.0
42.5°	27.4
45°	20.2
47.5°	14.5
50°	11.0
52.5°	9.1
55°	8.0
57.5°	6.8
60°	6.1
62.5°	5.3
65°	4.6
67.5°	3.8
70°	3.0
72.5°	2.7
75°	2.3
77.5°	1.9
80°	1.5
82.5°	1.1
85°	0.8
87.5°	0.4



TEST NUMBER: P1296906
CATALOG NUMBER: P3AS13R35W2N902765DE010 E3DLP1GPH_4000K

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)