

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1299254

Luminaire Tested: P3AS17R15W2N902750DE010 E3PHLD1MW\_3500K

Issue Date: 1/29/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1299254  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2509-551-9)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/29/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS17R15W2N902750DE010 E3PHLD1MW\_3500K  
Description: 3in Adjustable Tunable White LED luminaire with, R15 optic, 3500K CCT AND, 90CRI ,  
E3PHLD1MW TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 799.0 lumens  
Efficiency: N/A  
Efficacy: 41.2 lumens/watt  
Spacing Criteria (0/90/45): 0.56 / 0.56 / 0.66  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 19.4  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1299254  
CATALOG NUMBER: P3AS17R15W2N902750DE010 E3PHLD1MW\_3500K

### Luminous Intensity Polar Plot





TEST NUMBER: P1299254

CATALOG NUMBER: P3AS17R15W2N902750DE010 E3PHLD1MW\_3500K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	112	108	105	102	109	106	103	101	102	100	97	98	96	95	95	93	92	90
2	104	98	93	89	102	97	92	88	93	89	86	90	87	84	87	85	82	80
3	98	90	84	79	96	88	83	78	85	81	77	83	79	75	81	77	74	72
4	92	82	76	70	90	81	75	70	79	73	69	77	72	68	75	71	67	66
5	86	76	69	64	84	75	68	63	73	67	63	71	66	62	70	65	62	60
6	81	71	63	58	79	70	63	58	68	62	58	67	61	57	65	60	57	55
7	77	66	59	54	75	65	58	54	64	58	53	62	57	53	61	56	53	51
8	72	61	55	50	71	61	54	50	60	54	49	59	53	49	58	53	49	47
9	69	58	51	47	68	57	51	46	56	50	46	55	50	46	54	49	46	44
10	65	54	48	44	64	54	48	44	53	47	43	52	47	43	52	47	43	42

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	232503
5°	217961
10°	178732
15°	138866
20°	109606
25°	87344
30°	70112
35°	57233
40°	47145
45°	39663
50°	34080
55°	29476
60°	26138
65°	22726
70°	20196
75°	16352
80°	13259
85°	8806

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 39663 cd/sqm



TEST NUMBER: P1299254

CATALOG NUMBER: P3AS17R15W2N902750DE010 E3PHLD1MW\_3500K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	88.4	11.1
10°-20°	171.3	21.4
20°-30°	166.5	20.8
30°-40°	134.6	16.8
40°-50°	99.9	12.5
50°-60°	69.8	8.7
60°-70°	43.7	5.5
70°-80°	20.8	2.6
80°-90°	3.8	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	426.3	53.4
0°-40°	560.9	70.2
0°-60°	730.6	91.4
0°-90°	799.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	799.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1060	
5°	990	88
15°	612	171
25°	361	167
35°	214	135
45°	128	100
55°	77	70
65°	44	44
75°	19	21
85°	4	4
90°	0	



TEST NUMBER: P1299254  
CATALOG NUMBER: P3AS17R15W2N902750DE010 E3PHLD1MW\_3500K

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	1060.3
2.5°	1042.8
5°	990.2
7.5°	906.1
10°	802.7
12.5°	701.1
15°	611.7
17.5°	536.3
20°	469.7
22.5°	411.9
25°	361.0
27.5°	315.5
30°	276.9
32.5°	243.6
35°	213.8
37.5°	187.5
40°	164.7
42.5°	145.5
45°	127.9
47.5°	113.9
50°	99.9
52.5°	87.6
55°	77.1
57.5°	68.4
60°	59.6
62.5°	50.8
65°	43.8
67.5°	36.8
70°	31.5
72.5°	24.5
75°	19.3
77.5°	14.0
80°	10.5
82.5°	5.3
85°	3.5
87.5°	0.0
90°	0.0

(END OF REPORT)