

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1297038

Luminaire Tested: P3AS13R40W2N902750DE010 E3DL1WMH_3000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1297038
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-23)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R40W2N902750DE010 E3DL1WMH_3000K
Description: 3in Adjustable Tunable White LED luminaire with, R40 optic, 3000K CCT AND, 90CRI ,
E3DL1WMH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 890.0 lumens
Efficiency: N/A
Efficacy: 72.4 lumens/watt
Spacing Criteria (0/90/45): 0.65 / 0.65 / 0.63
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 12.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1297038
CATALOG NUMBER: P3AS13R40W2N902750DE010 E3DL1WMH_3000K

Luminous Intensity Polar Plot





TEST NUMBER: P1297038
 CATALOG NUMBER: P3AS13R40W2N902750DE010 E3DL1WMH_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	102	102	102	100
1	114	111	109	107	112	109	107	105	105	104	102	102	100	99	98	97	96	96	96	96	94
2	109	105	101	98	107	103	100	97	100	97	95	97	95	93	94	92	91	91	91	91	89
3	104	99	94	91	102	97	93	90	95	91	88	92	89	87	90	88	86	86	86	86	84
4	100	93	88	85	98	92	88	84	90	86	83	88	85	82	86	84	81	81	81	81	80
5	96	88	83	79	94	88	83	79	86	82	78	84	81	78	83	80	77	77	77	77	76
6	92	84	79	75	91	83	78	75	82	78	74	81	77	74	79	76	73	73	73	73	72
7	88	80	75	71	87	79	74	71	78	74	71	77	73	70	76	73	70	70	70	70	69
8	85	76	71	68	84	76	71	67	75	70	67	74	70	67	73	69	67	67	67	67	65
9	82	73	68	64	81	73	68	64	72	67	64	71	67	64	70	66	64	64	64	64	63
10	78	70	65	62	78	70	65	61	69	64	61	68	64	61	67	64	61	61	61	61	60

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	393828
5°	382367
10°	346999
15°	286653
20°	206775
25°	127894
30°	69251
35°	35790
40°	19465
45°	10885
50°	5458
55°	4091
60°	3684
65°	3580
70°	3398
75°	3219
80°	2904
85°	2013

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 10885 cd/sqm



TEST NUMBER: P1297038

CATALOG NUMBER: P3AS13R40W2N902750DE010 E3DL1WMH_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	160.1	18.0
10°-20°	343.8	38.6
20°-30°	245.4	27.6
30°-40°	90.3	10.1
40°-50°	28.4	3.2
50°-60°	9.9	1.1
60°-70°	6.8	0.8
70°-80°	4.0	0.5
80°-90°	1.2	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	749.3	84.2
0°-40°	839.7	94.3
0°-60°	878.0	98.7
0°-90°	890.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	890.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1796	
5°	1737	160
15°	1263	344
25°	529	245
35°	134	90
45°	35	28
55°	11	10
65°	7	7
75°	4	4
85°	1	1
90°	0	



TEST NUMBER: P1297038
CATALOG NUMBER: P3AS13R40W2N902750DE010 E3DL1WMH_3000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	1796.0
2.5°	1782.2
5°	1737.1
7.5°	1662.3
10°	1558.4
12.5°	1426.2
15°	1262.7
17.5°	1079.4
20°	886.1
22.5°	695.9
25°	528.6
27.5°	388.1
30°	273.5
32.5°	191.7
35°	133.7
37.5°	94.7
40°	68.0
42.5°	48.9
45°	35.1
47.5°	23.7
50°	16.0
52.5°	11.5
55°	10.7
57.5°	9.9
60°	8.4
62.5°	7.6
65°	6.9
67.5°	6.1
70°	5.3
72.5°	4.6
75°	3.8
77.5°	3.1
80°	2.3
82.5°	1.5
85°	0.8
87.5°	0.8
90°	0.0

(END OF REPORT)