

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1297061

Luminaire Tested: P3AS13R40W2N902750DE010 E3DLD1MW_5000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1297061
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-22)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R40W2N902750DE010 E3DLD1MW_5000K
Description: 3in Adjustable Tunable White LED luminaire with, R40 optic, 5000K CCT AND, 90CRI ,
E3DLD1MW TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 689.0 lumens
Efficiency: N/A
Efficacy: 56.0 lumens/watt
Spacing Criteria (0/90/45): 0.83 / 0.83 / 0.88
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 12.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1297061
CATALOG NUMBER: P3AS13R40W2N902750DE010 E3DLD1MW_5000K

Luminous Intensity Polar Plot





TEST NUMBER: P1297061

CATALOG NUMBER: P3AS13R40W2N902750DE010 E3DLD1MW_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	112	109	106	104	110	107	104	102	103	101	99	99	98	96	96	94	93	91
2	106	100	96	92	104	98	94	91	95	92	89	92	89	87	89	87	85	83
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76
4	94	85	79	74	92	84	78	74	82	77	73	80	75	72	78	74	71	69
5	89	79	73	68	87	78	72	67	76	71	67	75	70	66	73	69	66	64
6	84	74	67	62	82	73	67	62	71	66	61	70	65	61	68	64	61	59
7	79	69	62	57	78	68	62	57	67	61	57	65	60	57	64	60	56	55
8	75	64	58	53	74	64	57	53	63	57	53	62	56	53	61	56	52	51
9	71	60	54	50	70	60	54	50	59	53	49	58	53	49	57	52	49	48
10	67	57	51	46	66	56	50	46	56	50	46	55	50	46	54	49	46	45

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	154659
5°	151860
10°	143150
15°	130012
20°	114227
25°	97554
30°	80797
35°	62319
40°	44340
45°	29895
50°	16307
55°	11507
60°	10832
65°	10014
70°	8912
75°	8472
80°	6819
85°	5787

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 29895 cd/sqm



TEST NUMBER: P1297061
 CATALOG NUMBER: P3AS13R40W2N902750DE010 E3DLD1MW_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	64.3	9.3
10°-20°	159.5	23.2
20°-30°	184.5	26.8
30°-40°	145.3	21.1
40°-50°	74.6	10.8
50°-60°	28.5	4.1
60°-70°	18.9	2.7
70°-80°	10.3	1.5
80°-90°	3.0	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	408.3	59.3
0°-40°	553.7	80.4
0°-60°	656.8	95.3
0°-90°	689.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	689.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	705	
5°	690	64
15°	573	160
25°	403	184
35°	233	145
45°	96	75
55°	30	29
65°	19	19
75°	10	10
85°	2	3
90°	0	



TEST NUMBER: P1297061
CATALOG NUMBER: P3AS13R40W2N902750DE010 E3DLD1MW_5000K

CANDELA DISTRIBUTION (FULL):

	0°
0°	705.3
2.5°	701.5
5°	689.9
7.5°	669.9
10°	642.9
12.5°	611.3
15°	572.7
17.5°	532.7
20°	489.5
22.5°	445.6
25°	403.2
27.5°	360.8
30°	319.1
32.5°	276.7
35°	232.8
37.5°	191.9
40°	154.9
42.5°	123.3
45°	96.4
47.5°	70.1
50°	47.8
52.5°	34.7
55°	30.1
57.5°	27.0
60°	24.7
62.5°	21.6
65°	19.3
67.5°	16.2
70°	13.9
72.5°	11.6
75°	10.0
77.5°	7.7
80°	5.4
82.5°	4.6
85°	2.3
87.5°	1.5
90°	0.0

(END OF REPORT)