

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1297076

Luminaire Tested: P3AS13R40W2N902750DE010 E3DLP1GPH_5000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1297076
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-21)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R40W2N902750DE010 E3DLP1GPH_5000K
Description: 3in Adjustable Tunable White LED luminaire with, R40 optic, 5000K CCT AND, 90CRI ,
E3DLP1GPH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 278.0 lumens
Efficiency: N/A
Efficacy: 22.6 lumens/watt
Spacing Criteria (0/90/45): 0.73 / 0.73 / 0.74
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 12.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1297076
CATALOG NUMBER: P3AS13R40W2N902750DE010 E3DLP1GPH_5000K

Luminous Intensity Polar Plot





TEST NUMBER: P1297076

CATALOG NUMBER: P3AS13R40W2N902750DE010 E3DLP1GPH_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	35.8	12.9
10°-20°	83.5	30.0
20°-30°	78.7	28.3
30°-40°	45.5	16.4
40°-50°	18.1	6.5
50°-60°	8.0	2.9
60°-70°	5.0	1.8
70°-80°	2.6	0.9
80°-90°	0.8	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	198.0	71.2
0°-40°	243.5	87.6
0°-60°	269.6	97.0
0°-90°	278.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	278.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	395	
5°	385	36
15°	303	84
25°	172	79
35°	72	45
45°	22	18
55°	9	8
65°	5	5
75°	2	3
85°	1	1
90°	0	



TEST NUMBER: P1297076
CATALOG NUMBER: P3AS13R40W2N902750DE010 E3DLP1GPH_5000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	394.8
2.5°	392.5
5°	385.3
7.5°	372.0
10°	354.6
12.5°	331.2
15°	303.2
17.5°	271.8
20°	237.7
22.5°	203.6
25°	171.8
27.5°	142.3
30°	115.4
32.5°	92.0
35°	71.5
37.5°	54.1
40°	40.5
42.5°	30.3
45°	22.3
47.5°	16.3
50°	12.1
52.5°	9.8
55°	8.7
57.5°	7.9
60°	6.8
62.5°	5.7
65°	4.9
67.5°	4.2
70°	3.8
72.5°	3.0
75°	2.3
77.5°	1.9
80°	1.5
82.5°	1.1
85°	0.8
87.5°	0.4
90°	0.0

(END OF REPORT)