

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1297145

Luminaire Tested: P3AS13R40W2N902765DE010 E3D1LI_3000K

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1297145
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-12)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R40W2N902765DE010 E3D1LI_3000K
Description: 3in Adjustable Tunable White LED luminaire with, R40 optic, 3000K CCT AND, 90CRI ,
E3D1LI TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1070.0 lumens
Efficiency: N/A
Efficacy: 87.0 lumens/watt
Spacing Criteria (0/90/45): 0.7 / 0.7 / 0.6
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 12.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1297145
CATALOG NUMBER: P3AS13R40W2N902765DE010 E3D1LI_3000K

Luminous Intensity Polar Plot





TEST NUMBER: P1297145

CATALOG NUMBER: P3AS13R40W2N902765DE010 E3D1LI_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

| | | | | | | | | | | | | | | | | | | | | | |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|
| RF | 20 | | | | 20 | | | | 20 | | | | 20 | | | | 20 | | | | |
| RC | 80 | | | | 70 | | | | 50 | | | | 30 | | | | 10 | | | 0 | |
| RW | 70 | 50 | 30 | 10 | 70 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 0 |
| RCR | | | | | | | | | | | | | | | | | | | | | |
| 0 | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 | 100 | 100 | 100 |
| 1 | 115 | 112 | 110 | 109 | 112 | 110 | 109 | 107 | 106 | 105 | 104 | 103 | 102 | 101 | 99 | 98 | 98 | 96 | 96 | 96 | 96 |
| 2 | 111 | 107 | 104 | 101 | 109 | 105 | 102 | 100 | 102 | 100 | 98 | 99 | 97 | 96 | 96 | 95 | 94 | 92 | 92 | 92 | 92 |
| 3 | 107 | 102 | 98 | 95 | 105 | 100 | 97 | 94 | 98 | 95 | 93 | 96 | 93 | 91 | 93 | 91 | 90 | 88 | 88 | 88 | 88 |
| 4 | 103 | 97 | 93 | 90 | 101 | 96 | 92 | 89 | 94 | 91 | 88 | 92 | 89 | 87 | 90 | 88 | 86 | 85 | 85 | 85 | 85 |
| 5 | 99 | 93 | 89 | 85 | 98 | 92 | 88 | 85 | 91 | 87 | 84 | 89 | 86 | 84 | 88 | 85 | 83 | 82 | 82 | 82 | 82 |
| 6 | 96 | 89 | 85 | 81 | 95 | 89 | 84 | 81 | 87 | 83 | 81 | 86 | 83 | 80 | 85 | 82 | 80 | 79 | 79 | 79 | 79 |
| 7 | 93 | 86 | 81 | 78 | 92 | 85 | 81 | 78 | 84 | 80 | 77 | 83 | 80 | 77 | 82 | 79 | 77 | 76 | 76 | 76 | 76 |
| 8 | 90 | 83 | 78 | 75 | 89 | 82 | 78 | 75 | 81 | 77 | 75 | 80 | 77 | 74 | 79 | 76 | 74 | 73 | 73 | 73 | 73 |
| 9 | 87 | 80 | 75 | 72 | 86 | 79 | 75 | 72 | 78 | 75 | 72 | 78 | 74 | 72 | 77 | 74 | 71 | 70 | 70 | 70 | 70 |
| 10 | 84 | 77 | 72 | 70 | 83 | 77 | 72 | 69 | 76 | 72 | 69 | 75 | 72 | 69 | 74 | 71 | 69 | 68 | 68 | 68 | 68 |

AVERAGE LUMINANCE (cd/sqm):

| | |
|-----|--------|
| | 0° |
| 0° | 545395 |
| 5° | 541469 |
| 10° | 527289 |
| 15° | 471013 |
| 20° | 312320 |
| 25° | 117007 |
| 30° | 31296 |
| 35° | 12234 |
| 40° | 4408 |
| 45° | 2078 |
| 50° | 648 |
| 55° | 268 |
| 60° | 175 |
| 65° | 208 |
| 70° | 0 |
| 75° | 0 |
| 80° | 0 |
| 85° | 0 |

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 2078 cd/sqm



TEST NUMBER: P1297145

CATALOG NUMBER: P3AS13R40W2N902765DE010 E3D1LI_3000K

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10° | 232.1 | 21.7 |
| 10°-20° | 549.8 | 51.4 |
| 20°-30° | 249.3 | 23.3 |
| 30°-40° | 32.3 | 3.0 |
| 40°-50° | 5.6 | 0.5 |
| 50°-60° | 0.7 | 0.1 |
| 60°-70° | 0.2 | 0.0 |
| 70°-80° | 0.0 | 0.0 |
| 80°-90° | 0.0 | 0.0 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-30° | 1031.2 | 96.4 |
| 0°-40° | 1063.5 | 99.4 |
| 0°-60° | 1069.8 | 100.0 |
| 0°-90° | 1070.0 | 100.0 |
| 90°-120° | 0.0 | 0.0 |
| 90°-150° | 0.0 | 0.0 |
| 90°-180° | 0.0 | 0.0 |
| 0°-180° | 1070.0 | 100.0 |

CANDELA DISTRIBUTION:

| | 0° | Flux |
|-----|------|------|
| 0° | 2487 | |
| 5° | 2460 | 232 |
| 15° | 2075 | 550 |
| 25° | 484 | 249 |
| 35° | 46 | 32 |
| 45° | 7 | 6 |
| 55° | 1 | 1 |
| 65° | 0 | 0 |
| 75° | 0 | 0 |
| 85° | 0 | 0 |
| 90° | 0 | |



TEST NUMBER: P1297145

CATALOG NUMBER: P3AS13R40W2N902765DE010 E3D1LI_3000K

CANDELA DISTRIBUTION (FULL):

| 0° | |
|-------|--------|
| 0° | 2487.2 |
| 1° | 2485.7 |
| 2° | 2482.0 |
| 3° | 2476.4 |
| 4° | 2469.3 |
| 5° | 2459.9 |
| 6° | 2449.0 |
| 7° | 2435.5 |
| 8° | 2419.1 |
| 9° | 2396.6 |
| 10° | 2368.1 |
| 11° | 2334.8 |
| 12° | 2290.2 |
| 13° | 2235.1 |
| 14° | 2163.2 |
| 15° | 2074.8 |
| 16° | 1962.1 |
| 17° | 1833.6 |
| 18° | 1679.3 |
| 19° | 1516.3 |
| 20° | 1338.4 |
| 21° | 1160.5 |
| 22° | 985.2 |
| 23° | 810.6 |
| 24° | 639.0 |
| 25° | 483.6 |
| 26° | 358.1 |
| 27° | 262.2 |
| 28° | 197.0 |
| 29° | 153.2 |
| 30° | 123.6 |
| 31° | 102.3 |
| 32° | 85.4 |
| 32.5° | 77.9 |
| 33° | 70.4 |
| 34° | 57.3 |
| 35° | 45.7 |
| 36° | 36.0 |
| 37° | 28.5 |
| 37.5° | 25.5 |
| 38° | 22.5 |
| 39° | 18.7 |
| 40° | 15.4 |
| 42.5° | 10.1 |
| 45° | 6.7 |



TEST NUMBER: P1297145

CATALOG NUMBER: P3AS13R40W2N902765DE010 E3D1LI_3000K

CANDELA DISTRIBUTION (continued):

| | 0° |
|-------|-----|
| 47.5° | 4.1 |
| 50° | 1.9 |
| 52.5° | 0.7 |
| 55° | 0.7 |
| 57.5° | 0.4 |
| 60° | 0.4 |
| 62.5° | 0.4 |
| 65° | 0.4 |
| 67.5° | 0.0 |
| 70° | 0.0 |
| 72.5° | 0.0 |
| 75° | 0.0 |
| 77.5° | 0.0 |
| 80° | 0.0 |
| 82.5° | 0.0 |
| 85° | 0.0 |
| 87.5° | 0.0 |
| 90° | 0.0 |

(END OF REPORT)