

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1299558

Luminaire Tested: P3AS17R20W2N902750DE010 E3DLD1WH_5000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1299558
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-6)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R20W2N902750DE010 E3DLD1WH_5000K
Description: 3in Adjustable Tunable White LED luminaire with, R20 optic, 5000K CCT AND, 90CRI ,
E3DLD1WH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 948.9 lumens
Efficiency: N/A
Efficacy: 48.9 lumens/watt
Spacing Criteria (0/90/45): 0.76 / 0.76 / 0.83
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 19.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1299558
CATALOG NUMBER: P3AS17R20W2N902750DE010 E3DLD1WH_5000K

Luminous Intensity Polar Plot





TEST NUMBER: P1299558

CATALOG NUMBER: P3AS17R20W2N902750DE010 E3DLD1WH_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	96.0	10.1
10°-20°	226.9	23.9
20°-30°	251.8	26.5
30°-40°	192.1	20.2
40°-50°	98.4	10.4
50°-60°	40.4	4.3
60°-70°	25.2	2.7
70°-80°	14.1	1.5
80°-90°	4.1	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	574.7	60.6
0°-40°	766.8	80.8
0°-60°	905.5	95.4
0°-90°	948.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	948.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1070	
5°	1038	96
15°	815	227
25°	551	252
35°	306	192
45°	124	98
55°	41	40
65°	25	25
75°	13	14
85°	4	4
90°	0	



TEST NUMBER: P1299558
CATALOG NUMBER: P3AS17R20W2N902750DE010 E3DLD1WH_5000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	1070.5
1°	1071.7
2°	1066.9
3°	1060.8
4°	1051.2
5°	1037.9
6°	1022.3
7°	1005.4
8°	987.3
9°	965.6
10°	943.9
12.5°	881.2
15°	814.9
17.5°	747.4
20°	679.9
22.5°	612.4
25°	550.9
27.5°	489.4
30°	425.5
32.5°	365.3
35°	306.2
37.5°	254.4
40°	203.7
42.5°	160.3
45°	124.2
47.5°	94.0
50°	69.9
52.5°	51.8
55°	41.0
57.5°	37.4
60°	32.5
62.5°	28.9
65°	25.3
67.5°	21.7
70°	19.3
72.5°	15.7
75°	13.3
77.5°	10.8
80°	8.4
82.5°	6.0
85°	3.6
87.5°	1.2
90°	0.0

(END OF REPORT)