

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1297198

Luminaire Tested: P3AS13R40W2N902765DE010 E3DL1WMH\_2700K

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1297198  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-23)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS13R40W2N902765DE010 E3DL1WMH\_2700K  
Description: 3in Adjustable Tunable White LED luminaire with, R40 optic, 2700K CCT AND, 90CRI ,  
E3DL1WMH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 807.0 lumens  
Efficiency: N/A  
Efficacy: 65.6 lumens/watt  
Spacing Criteria (0/90/45): 0.65 / 0.65 / 0.63  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 12.3  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1297198  
CATALOG NUMBER: P3AS13R40W2N902765DE010 E3DL1WMH\_2700K

### Luminous Intensity Polar Plot





TEST NUMBER: P1297198

CATALOG NUMBER: P3AS13R40W2N902765DE010 E3DL1WMH\_2700K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|
| RF  | 20  |     |     |     | 20  |     |     |     | 20  |     |     |     | 20  |     |     |     | 20  |     |     |     |     |
| RC  | 80  |     |     |     | 70  |     |     |     | 50  |     |     |     | 30  |     |     |     | 10  |     |     | 0   |     |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 0   |
| RCR |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 102 | 102 | 102 | 100 |
| 1   | 114 | 111 | 109 | 107 | 112 | 109 | 107 | 105 | 105 | 104 | 102 | 102 | 100 | 99  | 98  | 97  | 96  | 96  | 96  | 96  | 94  |
| 2   | 109 | 105 | 101 | 98  | 107 | 103 | 100 | 97  | 100 | 97  | 95  | 97  | 95  | 93  | 94  | 92  | 91  | 91  | 91  | 91  | 89  |
| 3   | 104 | 99  | 94  | 91  | 102 | 97  | 93  | 90  | 95  | 91  | 88  | 92  | 89  | 87  | 90  | 88  | 86  | 86  | 86  | 86  | 84  |
| 4   | 100 | 93  | 88  | 85  | 98  | 92  | 88  | 84  | 90  | 86  | 83  | 88  | 85  | 82  | 86  | 84  | 81  | 81  | 81  | 81  | 80  |
| 5   | 96  | 88  | 83  | 79  | 94  | 88  | 83  | 79  | 86  | 82  | 78  | 84  | 81  | 78  | 83  | 80  | 77  | 77  | 77  | 77  | 76  |
| 6   | 92  | 84  | 79  | 75  | 91  | 83  | 78  | 75  | 82  | 78  | 74  | 81  | 77  | 74  | 79  | 76  | 73  | 73  | 73  | 73  | 72  |
| 7   | 88  | 80  | 75  | 71  | 87  | 79  | 74  | 71  | 78  | 74  | 71  | 77  | 73  | 70  | 76  | 73  | 70  | 70  | 70  | 70  | 69  |
| 8   | 85  | 76  | 71  | 68  | 84  | 76  | 71  | 67  | 75  | 70  | 67  | 74  | 70  | 67  | 73  | 69  | 67  | 67  | 67  | 67  | 65  |
| 9   | 82  | 73  | 68  | 64  | 81  | 73  | 68  | 64  | 72  | 67  | 64  | 71  | 67  | 64  | 70  | 66  | 64  | 64  | 64  | 64  | 63  |
| 10  | 78  | 70  | 65  | 62  | 78  | 70  | 65  | 61  | 69  | 64  | 61  | 68  | 64  | 61  | 67  | 64  | 61  | 61  | 61  | 61  | 60  |

**AVERAGE LUMINANCE (cd/sqm):**

|     |        |
|-----|--------|
|     | 0°     |
| 0°  | 357099 |
| 5°  | 346708 |
| 10° | 314623 |
| 15° | 259933 |
| 20° | 187500 |
| 25° | 115966 |
| 30° | 62794  |
| 35° | 32444  |
| 40° | 17633  |
| 45° | 9892   |
| 50° | 4947   |
| 55° | 3708   |
| 60° | 3333   |
| 65° | 3217   |
| 70° | 3077   |
| 75° | 2965   |
| 80° | 2652   |
| 85° | 1761   |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 9892 cd/sqm



TEST NUMBER: P1297198

CATALOG NUMBER: P3AS13R40W2N902765DE010 E3DL1WMH\_2700K

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 145.2  | 18.0      |
| 10°-20°   | 311.8  | 38.6      |
| 20°-30°   | 222.5  | 27.6      |
| 30°-40°   | 81.9   | 10.2      |
| 40°-50°   | 25.8   | 3.2       |
| 50°-60°   | 9.0    | 1.1       |
| 60°-70°   | 6.1    | 0.8       |
| 70°-80°   | 3.7    | 0.5       |
| 80°-90°   | 1.0    | 0.1       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-30°    | 679.5  | 84.2      |
| 0°-40°    | 761.4  | 94.3      |
| 0°-60°    | 796.1  | 98.7      |
| 0°-90°    | 807.0  | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 807.0  | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°   | Flux |
|-----|------|------|
| 0°  | 1628 |      |
| 5°  | 1575 | 145  |
| 15° | 1145 | 312  |
| 25° | 479  | 222  |
| 35° | 121  | 82   |
| 45° | 32   | 26   |
| 55° | 10   | 9    |
| 65° | 6    | 6    |
| 75° | 4    | 4    |
| 85° | 1    | 1    |
| 90° | 0    |      |



TEST NUMBER: P1297198  
CATALOG NUMBER: P3AS13R40W2N902765DE010 E3DL1WMH\_2700K

**CANDELA DISTRIBUTION (FULL):**

| 0°    |        |
|-------|--------|
| 0°    | 1628.5 |
| 2.5°  | 1616.0 |
| 5°    | 1575.1 |
| 7.5°  | 1507.3 |
| 10°   | 1413.0 |
| 12.5° | 1293.2 |
| 15°   | 1145.0 |
| 17.5° | 978.7  |
| 20°   | 803.5  |
| 22.5° | 631.0  |
| 25°   | 479.3  |
| 27.5° | 351.9  |
| 30°   | 248.0  |
| 32.5° | 173.9  |
| 35°   | 121.2  |
| 37.5° | 85.9   |
| 40°   | 61.6   |
| 42.5° | 44.3   |
| 45°   | 31.9   |
| 47.5° | 21.5   |
| 50°   | 14.5   |
| 52.5° | 10.4   |
| 55°   | 9.7    |
| 57.5° | 9.0    |
| 60°   | 7.6    |
| 62.5° | 6.9    |
| 65°   | 6.2    |
| 67.5° | 5.5    |
| 70°   | 4.8    |
| 72.5° | 4.2    |
| 75°   | 3.5    |
| 77.5° | 2.8    |
| 80°   | 2.1    |
| 82.5° | 1.4    |
| 85°   | 0.7    |
| 87.5° | 0.7    |
| 90°   | 0.0    |

(END OF REPORT)