

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1297308

Luminaire Tested: P3AS13R45W2N902750DE010 E3D1MW_3500K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1297308
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-28)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R45W2N902750DE010 E3D1MW_3500K
Description: 3in Adjustable Tunable White LED luminaire with, R45 optic, 3500K CCT AND, 90CRI ,
E3D1MW TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1040.1 lumens
Efficiency: N/A
Efficacy: 84.6 lumens/watt
Spacing Criteria (0/90/45): 0.72 / 0.72 / 0.66
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 12.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1297308
CATALOG NUMBER: P3AS13R45W2N902750DE010 E3D1MW_3500K

Luminous Intensity Polar Plot





TEST NUMBER: P1297308

CATALOG NUMBER: P3AS13R45W2N902750DE010 E3D1MW_3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	102	102	102	100
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	97	97	97	95
2	110	106	102	100	108	104	101	98	101	98	96	98	96	94	95	94	92	92	92	92	91
3	106	100	96	93	104	99	95	92	96	93	91	94	91	89	92	90	88	88	88	88	86
4	102	95	91	87	100	94	90	87	92	89	86	90	87	85	88	86	84	84	84	84	82
5	98	91	86	82	96	90	85	82	88	84	81	87	83	81	85	82	80	80	80	80	79
6	94	87	82	78	93	86	81	78	85	80	77	83	80	77	82	79	76	76	76	76	75
7	90	83	78	74	89	82	78	74	81	77	74	80	76	74	79	76	73	73	73	73	72
8	87	79	74	71	86	79	74	71	78	74	71	77	73	70	76	73	70	70	70	70	69
9	84	76	71	68	83	76	71	68	75	71	68	74	70	67	73	70	67	67	67	67	66
10	81	73	68	65	80	73	68	65	72	68	65	71	67	65	71	67	65	65	65	65	64

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	450907
5°	453312
10°	439382
15°	368197
20°	281448
25°	171349
30°	71302
35°	22834
40°	7099
45°	1458
50°	1058
55°	1185
60°	1009
65°	1193
70°	1026
75°	1356
80°	1010
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 1458 cd/sqm



TEST NUMBER: P1297308

CATALOG NUMBER: P3AS13R45W2N902750DE010 E3D1MW_3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	194.2	18.7
10°-20°	445.8	42.9
20°-30°	321.0	30.9
30°-40°	66.8	6.4
40°-50°	6.1	0.6
50°-60°	2.5	0.2
60°-70°	2.0	0.2
70°-80°	1.4	0.1
80°-90°	0.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	961.0	92.4
0°-40°	1027.7	98.8
0°-60°	1036.4	99.6
0°-90°	1040.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1040.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2056	
5°	2059	194
15°	1622	446
25°	708	321
35°	85	67
45°	5	6
55°	3	3
65°	2	2
75°	2	1
85°	0	0
90°	0	



TEST NUMBER: P1297308
CATALOG NUMBER: P3AS13R45W2N902750DE010 E3D1MW_3500K

CANDELA DISTRIBUTION (FULL):

0°	
0°	2056.3
2.5°	2057.0
5°	2059.4
7.5°	2044.6
10°	1973.3
12.5°	1824.3
15°	1621.9
17.5°	1414.8
20°	1206.1
22.5°	966.5
25°	708.2
27.5°	466.9
30°	281.6
32.5°	157.5
35°	85.3
37.5°	48.1
40°	24.8
42.5°	10.9
45°	4.7
47.5°	3.1
50°	3.1
52.5°	3.1
55°	3.1
57.5°	2.3
60°	2.3
62.5°	2.3
65°	2.3
67.5°	1.6
70°	1.6
72.5°	1.6
75°	1.6
77.5°	0.8
80°	0.8
82.5°	0.8
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)