

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1299670

Luminaire Tested: P3AS17R20W2N902765DE010 E3DL1MW_3500K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1299670
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-7)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R20W2N902765DE010 E3DL1MW_3500K
Description: 3in Adjustable Tunable White LED luminaire with, R20 optic, 3500K CCT AND, 90CRI ,
E3DL1MW TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1254.0 lumens
Efficiency: N/A
Efficacy: 64.6 lumens/watt
Spacing Criteria (0/90/45): 0.44 / 0.44 / 0.46
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 19.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1299670
CATALOG NUMBER: P3AS17R20W2N902765DE010 E3DL1MW_3500K

Luminous Intensity Polar Plot





TEST NUMBER: P1299670

CATALOG NUMBER: P3AS17R20W2N902765DE010 E3DL1MW_3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95
2	110	106	102	100	108	104	101	98	101	98	96	98	96	94	95	94	92	91
3	106	100	96	93	104	99	95	92	97	93	91	94	92	89	92	90	88	87
4	102	96	91	88	100	95	90	87	92	89	86	91	88	85	89	86	84	83
5	98	91	87	83	97	90	86	83	89	85	82	87	84	81	86	83	81	79
6	95	87	83	79	93	87	82	79	85	81	78	84	81	78	83	80	77	76
7	91	84	79	76	90	83	79	76	82	78	75	81	78	75	80	77	75	73
8	88	81	76	73	87	80	76	73	79	75	72	78	75	72	78	74	72	71
9	85	78	73	70	85	77	73	70	77	73	70	76	72	69	75	72	69	68
10	83	75	71	68	82	75	70	67	74	70	67	73	70	67	73	69	67	66

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	964813
5°	877039
10°	648173
15°	400978
20°	228990
25°	130725
30°	73302
35°	39886
40°	21841
45°	12032
50°	7027
55°	5085
60°	4780
65°	4410
70°	3911
75°	4067
80°	3031
85°	3019

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 12032 cd/sqm



TEST NUMBER: P1299670

CATALOG NUMBER: P3AS17R20W2N902765DE010 E3DL1MW_3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	345.0	27.5
10°-20°	492.5	39.3
20°-30°	257.1	20.5
30°-40°	99.4	7.9
40°-50°	32.3	2.6
50°-60°	12.7	1.0
60°-70°	8.4	0.7
70°-80°	4.9	0.4
80°-90°	1.6	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1094.7	87.3
0°-40°	1194.1	95.2
0°-60°	1239.0	98.8
0°-90°	1254.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1254.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4400	
5°	3984	345
15°	1766	493
25°	540	257
35°	149	99
45°	39	32
55°	13	13
65°	8	8
75°	5	5
85°	1	2
90°	0	



TEST NUMBER: P1299670
CATALOG NUMBER: P3AS17R20W2N902765DE010 E3DL1MW_3500K

CANDELA DISTRIBUTION (FULL):

0°	
0°	4399.9
1°	4391.4
2°	4339.3
3°	4259.4
4°	4135.8
5°	3984.4
6°	3805.1
7°	3606.4
8°	3376.2
9°	3152.1
10°	2911.0
12.5°	2313.8
15°	1766.3
17.5°	1321.7
20°	981.3
22.5°	726.9
25°	540.3
27.5°	398.6
30°	289.5
32.5°	209.6
35°	149.0
37.5°	107.8
40°	76.3
42.5°	54.5
45°	38.8
47.5°	27.9
50°	20.6
52.5°	15.7
55°	13.3
57.5°	12.1
60°	10.9
62.5°	9.7
65°	8.5
67.5°	7.3
70°	6.1
72.5°	6.1
75°	4.8
77.5°	3.6
80°	2.4
82.5°	2.4
85°	1.2
87.5°	1.2
90°	0.0

(END OF REPORT)