

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1297316

Luminaire Tested: P3AS13R45W2N902750DE010 E3DL1H\_2700K

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1297316  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-27)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS13R45W2N902750DE010 E3DL1H\_2700K  
Description: 3in Adjustable Tunable White LED luminaire with, R45 optic, 2700K CCT AND, 90CRI ,  
E3DL1H TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 775.0 lumens  
Efficiency: N/A  
Efficacy: 63.0 lumens/watt  
Spacing Criteria (0/90/45): 0.69 / 0.69 / 0.69  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 12.3  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1297316  
CATALOG NUMBER: P3AS13R45W2N902750DE010 E3DL1H\_2700K

### Luminous Intensity Polar Plot





TEST NUMBER: P1297316  
 CATALOG NUMBER: P3AS13R45W2N902750DE010 E3DL1H\_2700K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	114	111	109	107	111	109	107	105	105	103	102	101	100	99	98	97	96	94	94	94	94
2	109	104	100	97	106	102	99	96	99	96	94	96	94	92	93	91	90	88	88	88	88
3	104	98	93	89	102	96	92	88	94	90	87	91	88	86	89	86	84	83	83	83	83
4	99	92	87	83	97	91	86	82	89	85	81	87	83	80	85	82	79	78	78	78	78
5	94	87	81	77	93	86	81	77	84	80	76	82	79	76	81	78	75	74	74	74	74
6	90	82	76	73	89	81	76	72	80	75	72	78	74	71	77	74	71	70	70	70	70
7	86	78	72	68	85	77	72	68	76	71	68	75	71	67	74	70	67	66	66	66	66
8	83	74	68	65	82	73	68	64	72	68	64	71	67	64	70	67	64	62	62	62	62
9	79	70	65	61	78	70	65	61	69	64	61	68	64	61	67	63	61	59	59	59	59
10	76	67	62	58	75	67	62	58	66	61	58	65	61	58	65	61	58	57	57	57	57

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	291029
5°	284217
10°	261273
15°	221386
20°	171748
25°	120055
30°	75632
35°	44517
40°	25190
45°	12249
50°	4264
55°	3441
60°	3333
65°	3217
70°	3142
75°	2965
80°	2652
85°	1761

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 12249 cd/sqm



TEST NUMBER: P1297316  
 CATALOG NUMBER: P3AS13R45W2N902750DE010 E3DL1H\_2700K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	119.5	15.4
10°-20°	267.8	34.6
20°-30°	227.4	29.3
30°-40°	108.5	14.0
40°-50°	32.7	4.2
50°-60°	8.3	1.1
60°-70°	6.1	0.8
70°-80°	3.7	0.5
80°-90°	1.0	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	614.7	79.3
0°-40°	723.2	93.3
0°-60°	764.1	98.6
0°-90°	775.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	775.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1327	
5°	1291	120
15°	975	268
25°	496	227
35°	166	108
45°	40	33
55°	9	8
65°	6	6
75°	4	4
85°	1	1
90°	0	



TEST NUMBER: P1297316  
CATALOG NUMBER: P3AS13R45W2N902750DE010 E3DL1H\_2700K

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	1327.2
2.5°	1318.9
5°	1291.2
7.5°	1243.4
10°	1173.4
12.5°	1080.5
15°	975.2
17.5°	858.0
20°	736.0
22.5°	612.0
25°	496.2
27.5°	390.9
30°	298.7
32.5°	224.6
35°	166.3
37.5°	122.7
40°	88.0
42.5°	61.0
45°	39.5
47.5°	22.2
50°	12.5
52.5°	9.7
55°	9.0
57.5°	8.3
60°	7.6
62.5°	6.9
65°	6.2
67.5°	5.5
70°	4.9
72.5°	4.2
75°	3.5
77.5°	2.8
80°	2.1
82.5°	1.4
85°	0.7
87.5°	0.7
90°	0.0

(END OF REPORT)