

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1299683

Luminaire Tested: P3AS17R20W2N902765DE010 E3DLD1GPH_4000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1299683
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-6)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R20W2N902765DE010 E3DLD1GPH_4000K
Description: 3in Adjustable Tunable White LED luminaire with, R20 optic, 4000K CCT AND, 90CRI ,
E3DLD1GPH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 468.1 lumens
Efficiency: N/A
Efficacy: 24.1 lumens/watt
Spacing Criteria (0/90/45): 0.76 / 0.76 / 0.83
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 19.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1299683
CATALOG NUMBER: P3AS17R20W2N902765DE010 E3DLD1GPH_4000K

Luminous Intensity Polar Plot





TEST NUMBER: P1299683

CATALOG NUMBER: P3AS17R20W2N902765DE010 E3DLD1GPH_4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	113	109	106	104	110	107	105	102	103	101	99	99	98	96	96	95	93	91
2	106	100	96	92	104	99	94	91	95	92	89	92	89	87	90	87	85	83
3	100	93	87	82	98	91	86	82	88	84	80	86	82	79	84	81	78	76
4	94	86	79	75	92	85	79	74	82	77	73	80	76	72	78	75	72	70
5	89	80	73	68	87	79	73	68	77	71	67	75	70	67	73	69	66	65
6	84	74	68	63	82	73	67	63	72	66	62	70	65	62	69	65	61	60
7	80	69	63	58	78	69	62	58	67	62	58	66	61	57	65	60	57	55
8	75	65	59	54	74	64	58	54	63	58	54	62	57	53	61	57	53	52
9	72	61	55	50	70	61	55	50	60	54	50	59	54	50	58	53	50	48
10	68	58	51	47	67	57	51	47	56	51	47	56	50	47	55	50	47	45

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	115758
5°	112679
10°	103650
15°	91238
20°	78243
25°	65738
30°	53147
35°	40422
40°	28768
45°	18979
50°	11769
55°	7723
60°	7061
65°	6486
70°	6091
75°	5507
80°	5304
85°	4529

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 18979 cd/sqm



TEST NUMBER: P1299683

CATALOG NUMBER: P3AS17R20W2N902765DE010 E3DLD1GPH_4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	47.4	10.1
10°-20°	111.9	23.9
20°-30°	124.2	26.5
30°-40°	94.7	20.2
40°-50°	48.5	10.4
50°-60°	19.9	4.3
60°-70°	12.4	2.7
70°-80°	7.0	1.5
80°-90°	2.0	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	283.4	60.6
0°-40°	378.2	80.8
0°-60°	446.6	95.4
0°-90°	468.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	468.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	528	
5°	512	47
15°	402	112
25°	272	124
35°	151	95
45°	61	49
55°	20	20
65°	12	12
75°	6	7
85°	2	2
90°	0	



TEST NUMBER: P1299683
CATALOG NUMBER: P3AS17R20W2N902765DE010 E3DLD1GPH_4000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	527.9
1°	528.5
2°	526.1
3°	523.2
4°	518.4
5°	511.9
6°	504.1
7°	495.8
8°	486.9
9°	476.2
10°	465.5
12.5°	434.6
15°	401.9
17.5°	368.6
20°	335.3
22.5°	302.0
25°	271.7
27.5°	241.4
30°	209.9
32.5°	180.1
35°	151.0
37.5°	125.4
40°	100.5
42.5°	79.1
45°	61.2
47.5°	46.4
50°	34.5
52.5°	25.6
55°	20.2
57.5°	18.4
60°	16.1
62.5°	14.3
65°	12.5
67.5°	10.7
70°	9.5
72.5°	7.7
75°	6.5
77.5°	5.4
80°	4.2
82.5°	3.0
85°	1.8
87.5°	0.6
90°	0.0

(END OF REPORT)