

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1297461

Luminaire Tested: P3AS13R45W2N902765DE010 E3DL1MW_2700K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1297461
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-27)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R45W2N902765DE010 E3DL1MW_2700K
Description: 3in Adjustable Tunable White LED luminaire with, R45 optic, 2700K CCT AND, 90CRI ,
E3DL1MW TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 775.0 lumens
Efficiency: N/A
Efficacy: 63.0 lumens/watt
Spacing Criteria (0/90/45): 0.69 / 0.69 / 0.69
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 12.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1297461
CATALOG NUMBER: P3AS13R45W2N902765DE010 E3DL1MW_2700K

Luminous Intensity Polar Plot





TEST NUMBER: P1297461

CATALOG NUMBER: P3AS13R45W2N902765DE010 E3DL1MW_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

| | | | | | | | | | | | | | | | | | | | | | |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|----|----|---|
| RF | 20 | | | | 20 | | | | 20 | | | | 20 | | | | 20 | | | | |
| RC | 80 | | | | 70 | | | | 50 | | | | 30 | | | | 10 | | | 0 | |
| RW | 70 | 50 | 30 | 10 | 70 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 0 |
| RCR | | | | | | | | | | | | | | | | | | | | | |
| 0 | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 | | | |
| 1 | 114 | 111 | 109 | 107 | 111 | 109 | 107 | 105 | 105 | 103 | 102 | 101 | 100 | 99 | 98 | 97 | 96 | 94 | | | |
| 2 | 109 | 104 | 100 | 97 | 106 | 102 | 99 | 96 | 99 | 96 | 94 | 96 | 94 | 92 | 93 | 91 | 90 | 88 | | | |
| 3 | 104 | 98 | 93 | 89 | 102 | 96 | 92 | 88 | 94 | 90 | 87 | 91 | 88 | 86 | 89 | 86 | 84 | 83 | | | |
| 4 | 99 | 92 | 87 | 83 | 97 | 91 | 86 | 82 | 89 | 85 | 81 | 87 | 83 | 80 | 85 | 82 | 79 | 78 | | | |
| 5 | 94 | 87 | 81 | 77 | 93 | 86 | 81 | 77 | 84 | 80 | 76 | 82 | 79 | 76 | 81 | 78 | 75 | 74 | | | |
| 6 | 90 | 82 | 76 | 73 | 89 | 81 | 76 | 72 | 80 | 75 | 72 | 78 | 74 | 71 | 77 | 74 | 71 | 70 | | | |
| 7 | 86 | 78 | 72 | 68 | 85 | 77 | 72 | 68 | 76 | 71 | 68 | 75 | 71 | 67 | 74 | 70 | 67 | 66 | | | |
| 8 | 83 | 74 | 68 | 65 | 82 | 73 | 68 | 64 | 72 | 68 | 64 | 71 | 67 | 64 | 70 | 67 | 64 | 62 | | | |
| 9 | 79 | 70 | 65 | 61 | 78 | 70 | 65 | 61 | 69 | 64 | 61 | 68 | 64 | 61 | 67 | 63 | 61 | 59 | | | |
| 10 | 76 | 67 | 62 | 58 | 75 | 67 | 62 | 58 | 66 | 61 | 58 | 65 | 61 | 58 | 65 | 61 | 58 | 57 | | | |

AVERAGE LUMINANCE (cd/sqm):

| | |
|-----|--------|
| | 0° |
| 0° | 291029 |
| 5° | 284217 |
| 10° | 261273 |
| 15° | 221386 |
| 20° | 171748 |
| 25° | 120055 |
| 30° | 75632 |
| 35° | 44517 |
| 40° | 25190 |
| 45° | 12249 |
| 50° | 4264 |
| 55° | 3441 |
| 60° | 3333 |
| 65° | 3217 |
| 70° | 3142 |
| 75° | 2965 |
| 80° | 2652 |
| 85° | 1761 |

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 12249 cd/sqm



TEST NUMBER: P1297461

CATALOG NUMBER: P3AS13R45W2N902765DE010 E3DL1MW_2700K

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10° | 119.5 | 15.4 |
| 10°-20° | 267.8 | 34.6 |
| 20°-30° | 227.4 | 29.3 |
| 30°-40° | 108.5 | 14.0 |
| 40°-50° | 32.7 | 4.2 |
| 50°-60° | 8.3 | 1.1 |
| 60°-70° | 6.1 | 0.8 |
| 70°-80° | 3.7 | 0.5 |
| 80°-90° | 1.0 | 0.1 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-30° | 614.7 | 79.3 |
| 0°-40° | 723.2 | 93.3 |
| 0°-60° | 764.1 | 98.6 |
| 0°-90° | 775.0 | 100.0 |
| 90°-120° | 0.0 | 0.0 |
| 90°-150° | 0.0 | 0.0 |
| 90°-180° | 0.0 | 0.0 |
| 0°-180° | 775.0 | 100.0 |

CANDELA DISTRIBUTION:

| | 0° | Flux |
|-----|------|------|
| 0° | 1327 | |
| 5° | 1291 | 120 |
| 15° | 975 | 268 |
| 25° | 496 | 227 |
| 35° | 166 | 108 |
| 45° | 40 | 33 |
| 55° | 9 | 8 |
| 65° | 6 | 6 |
| 75° | 4 | 4 |
| 85° | 1 | 1 |
| 90° | 0 | |



TEST NUMBER: P1297461
CATALOG NUMBER: P3AS13R45W2N902765DE010 E3DL1MW_2700K

CANDELA DISTRIBUTION (FULL):

| 0° | |
|-------|--------|
| 0° | 1327.2 |
| 2.5° | 1318.9 |
| 5° | 1291.2 |
| 7.5° | 1243.4 |
| 10° | 1173.4 |
| 12.5° | 1080.5 |
| 15° | 975.2 |
| 17.5° | 858.0 |
| 20° | 736.0 |
| 22.5° | 612.0 |
| 25° | 496.2 |
| 27.5° | 390.9 |
| 30° | 298.7 |
| 32.5° | 224.6 |
| 35° | 166.3 |
| 37.5° | 122.7 |
| 40° | 88.0 |
| 42.5° | 61.0 |
| 45° | 39.5 |
| 47.5° | 22.2 |
| 50° | 12.5 |
| 52.5° | 9.7 |
| 55° | 9.0 |
| 57.5° | 8.3 |
| 60° | 7.6 |
| 62.5° | 6.9 |
| 65° | 6.2 |
| 67.5° | 5.5 |
| 70° | 4.9 |
| 72.5° | 4.2 |
| 75° | 3.5 |
| 77.5° | 2.8 |
| 80° | 2.1 |
| 82.5° | 1.4 |
| 85° | 0.7 |
| 87.5° | 0.7 |
| 90° | 0.0 |

(END OF REPORT)