

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1299747

Luminaire Tested: P3AS17R25W2N902750DE010 E3CB1MMS_3500K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1299747
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-12)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R25W2N902750DE010 E3CB1MMS_3500K
Description: 3in Adjustable Tunable White LED luminaire with, R25 optic, 3500K CCT AND, 90CRI ,
E3CB1MMS TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1542.9 lumens
Efficiency: N/A
Efficacy: 79.5 lumens/watt
Spacing Criteria (0/90/45): 0.45 / 0.45 / 0.41
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 19.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1299747
CATALOG NUMBER: P3AS17R25W2N902750DE010 E3CB1MMS_3500K

Luminous Intensity Polar Plot





TEST NUMBER: P1299747

CATALOG NUMBER: P3AS17R25W2N902750DE010 E3CB1MMS_3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	99	99	100
1	115	113	111	110	113	111	109	108	107	106	105	103	103	102	100	99	99	97	97	97	97
2	112	108	105	103	110	107	104	102	104	102	100	101	99	98	98	97	96	94	94	94	94
3	108	104	101	98	107	103	100	97	100	98	96	98	96	94	96	94	93	92	92	92	92
4	105	100	97	94	104	99	96	93	97	95	92	96	93	91	94	92	90	89	89	89	89
5	103	97	93	90	101	96	93	90	95	92	89	93	91	89	92	90	88	87	87	87	87
6	100	94	90	87	99	93	90	87	92	89	87	91	88	86	90	87	86	85	85	85	85
7	97	91	88	85	96	91	87	85	90	87	84	89	86	84	88	85	83	83	83	83	83
8	95	89	85	83	94	89	85	82	88	84	82	87	84	82	86	83	81	81	81	81	81
9	93	87	83	80	92	86	83	80	86	82	80	85	82	80	84	82	80	79	79	79	79
10	91	85	81	78	90	84	81	78	84	80	78	83	80	78	82	80	78	77	77	77	77

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1649692
5°	1530042
10°	1186573
15°	594986
20°	195480
25°	77714
30°	29169
35°	8432
40°	3807
45°	1489
50°	1228
55°	918
60°	1053
65°	1245
70°	769
75°	1017
80°	1515
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 80°
 Luminance: 1515 cd/sqm



TEST NUMBER: P1299747

CATALOG NUMBER: P3AS17R25W2N902750DE010 E3CB1MMS_3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	611.4	39.6
10°-20°	729.4	47.3
20°-30°	164.4	10.7
30°-40°	26.6	1.7
40°-50°	4.8	0.3
50°-60°	2.5	0.2
60°-70°	2.2	0.1
70°-80°	1.3	0.1
80°-90°	0.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1505.3	97.6
0°-40°	1531.9	99.3
0°-60°	1539.2	99.8
0°-90°	1542.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1542.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	7523	
5°	6951	611
15°	2621	729
25°	321	164
35°	32	27
45°	5	5
55°	2	3
65°	2	2
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P1299747

CATALOG NUMBER: P3AS17R25W2N902750DE010 E3CB1MMS_3500K

CANDELA DISTRIBUTION (FULL):

0°	
0°	7523.2
1°	7511.1
2°	7450.5
3°	7338.9
4°	7170.4
5°	6951.0
6°	6689.2
7°	6405.5
8°	6080.6
9°	5725.4
10°	5329.0
11°	4872.0
12°	4345.9
13°	3795.5
14°	3205.2
15°	2620.9
17.5°	1493.5
20°	837.7
22.5°	505.5
25°	321.2
27.5°	197.6
30°	115.2
32.5°	60.6
35°	31.5
37.5°	20.6
40°	13.3
42.5°	8.5
45°	4.8
47.5°	3.6
50°	3.6
52.5°	3.6
55°	2.4
57.5°	2.4
60°	2.4
62.5°	2.4
65°	2.4
67.5°	2.4
70°	1.2
72.5°	1.2
75°	1.2
77.5°	1.2
80°	1.2
82.5°	0.0
85°	0.0
87.5°	0.0



TEST NUMBER: P1299747
CATALOG NUMBER: P3AS17R25W2N902750DE010 E3CB1MMS_3500K

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)