

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1299792

Luminaire Tested: P3AS17R25W2N902750DE010 E3D1WMH\_3500K

Issue Date: 1/29/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1299792  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-9)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/29/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS17R25W2N902750DE010 E3D1WMH\_3500K  
Description: 3in Adjustable Tunable White LED luminaire with, R25 optic, 3500K CCT AND, 90CRI ,  
E3D1WMH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1638.0 lumens  
Efficiency: N/A  
Efficacy: 84.4 lumens/watt  
Spacing Criteria (0/90/45): 0.44 / 0.44 / 0.4  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 19.4  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1299792  
CATALOG NUMBER: P3AS17R25W2N902750DE010 E3D1WMH\_3500K

### Luminous Intensity Polar Plot





TEST NUMBER: P1299792

CATALOG NUMBER: P3AS17R25W2N902750DE010 E3D1WMH\_3500K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	102	102	102	100
1	115	113	111	110	113	111	110	108	107	106	105	104	103	102	100	99	99	99	99	99	97
2	112	108	106	103	110	107	104	102	104	102	100	101	99	98	98	97	96	96	96	96	94
3	109	104	101	98	107	103	100	97	100	98	96	98	96	94	96	94	93	96	94	93	92
4	106	101	97	94	104	100	96	94	98	95	92	96	93	91	94	92	90	94	92	90	89
5	103	97	93	91	101	96	93	90	95	92	90	93	91	89	92	90	88	92	90	88	87
6	100	94	90	88	99	94	90	87	92	89	87	91	88	86	90	88	86	90	88	86	85
7	98	92	88	85	97	91	87	85	90	87	84	89	86	84	88	86	84	88	86	84	83
8	95	89	85	83	94	89	85	83	88	85	82	87	84	82	86	84	82	86	84	82	81
9	93	87	83	81	92	86	83	80	86	83	80	85	82	80	84	82	80	84	82	80	79
10	91	85	81	79	90	84	81	79	84	81	78	83	80	78	83	80	78	83	80	78	77

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	1793913
5°	1661805
10°	1285748
15°	614124
20°	202481
25°	85360
30°	33094
35°	14322
40°	4752
45°	2202
50°	819
55°	459
60°	263
65°	311
70°	0
75°	0
80°	0
85°	0

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 2202 cd/sqm



TEST NUMBER: P1299792

CATALOG NUMBER: P3AS17R25W2N902750DE010 E3D1WMH\_3500K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	663.6	40.5
10°-20°	754.8	46.1
20°-30°	175.4	10.7
30°-40°	36.8	2.2
40°-50°	6.0	0.4
50°-60°	1.0	0.1
60°-70°	0.5	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1593.8	97.3
0°-40°	1630.6	99.5
0°-60°	1637.5	100.0
0°-90°	1638.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1638.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	8181	
5°	7550	664
15°	2705	755
25°	353	175
35°	54	37
45°	7	6
55°	1	1
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P1299792  
CATALOG NUMBER: P3AS17R25W2N902750DE010 E3D1WMH\_3500K

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	8180.9
1°	8164.3
2°	8079.4
3°	7960.0
4°	7777.7
5°	7549.6
6°	7256.8
7°	6950.4
8°	6606.5
9°	6218.7
10°	5774.4
11°	5259.5
12°	4668.6
13°	4021.3
14°	3344.2
15°	2705.2
16°	2139.8
17°	1667.1
18°	1311.3
19°	1048.8
20°	867.7
21°	725.1
22°	608.7
23°	508.4
24°	425.2
25°	352.8
27.5°	209.1
30°	130.7
32.5°	83.7
35°	53.5
37.5°	32.1
40°	16.6
42.5°	10.7
45°	7.1
47.5°	4.2
50°	2.4
52.5°	1.2
55°	1.2
57.5°	0.6
60°	0.6
62.5°	0.6
65°	0.6
67.5°	0.6
70°	0.0
72.5°	0.0



TEST NUMBER: P1299792  
CATALOG NUMBER: P3AS17R25W2N902750DE010 E3D1WMH\_3500K

**CANDELA DISTRIBUTION (continued):**

	0°
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)