

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1297501

Luminaire Tested: P3AS13R45W2N902765DE010 E3DLD1MW\_5000K

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1297501  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-26)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS13R45W2N902765DE010 E3DLD1MW\_5000K  
Description: 3in Adjustable Tunable White LED luminaire with, R45 optic, 5000K CCT AND, 90CRI ,  
E3DLD1MW TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 669.0 lumens  
Efficiency: N/A  
Efficacy: 54.4 lumens/watt  
Spacing Criteria (0/90/45): 0.84 / 0.84 / 0.92  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 12.3  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1297501  
CATALOG NUMBER: P3AS13R45W2N902765DE010 E3DLD1MW\_5000K

### Luminous Intensity Polar Plot





TEST NUMBER: P1297501  
 CATALOG NUMBER: P3AS13R45W2N902765DE010 E3DLD1MW\_5000K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	112	109	106	104	110	107	104	102	103	101	99	99	97	96	96	94	93	91			91
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83			83
3	99	92	86	82	97	90	85	81	88	83	80	85	81	78	83	80	77	75			75
4	94	85	78	74	92	84	78	73	81	76	72	79	75	71	77	74	71	69			69
5	88	79	72	67	86	78	71	67	76	70	66	74	69	65	72	68	65	63			63
6	83	73	66	61	81	72	66	61	71	65	61	69	64	60	68	63	60	58			58
7	78	68	61	57	77	67	61	56	66	60	56	65	60	56	64	59	55	54			54
8	74	64	57	52	73	63	57	52	62	56	52	61	56	52	60	55	52	50			50
9	70	60	53	49	69	59	53	49	58	52	48	57	52	48	56	52	48	47			47
10	67	56	50	45	66	56	49	45	55	49	45	54	49	45	53	48	45	44			44

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	141853
5°	139335
10°	131839
15°	120250
20°	106339
25°	92328
30°	79253
35°	66040
40°	49206
45°	30112
50°	13953
55°	10896
60°	10482
65°	9599
70°	8912
75°	8472
80°	7829
85°	5787

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 30112 cd/sqm



TEST NUMBER: P1297501

CATALOG NUMBER: P3AS13R45W2N902765DE010 E3DLD1MW\_5000K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	59.1	8.8
10°-20°	147.5	22.0
20°-30°	175.2	26.2
30°-40°	152.2	22.8
40°-50°	76.3	11.4
50°-60°	26.5	4.0
60°-70°	18.6	2.8
70°-80°	10.4	1.6
80°-90°	3.1	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	381.8	57.1
0°-40°	534.0	79.8
0°-60°	636.9	95.2
0°-90°	669.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	669.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	647	
5°	633	59
15°	530	147
25°	382	175
35°	247	152
45°	97	76
55°	28	26
65°	18	19
75°	10	10
85°	2	3
90°	0	



TEST NUMBER: P1297501  
CATALOG NUMBER: P3AS13R45W2N902765DE010 E3DLD1MW\_5000K

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	646.9
2.5°	643.8
5°	633.0
7.5°	616.0
10°	592.1
12.5°	562.8
15°	529.7
17.5°	492.7
20°	455.7
22.5°	417.9
25°	381.6
27.5°	346.9
30°	313.0
32.5°	280.6
35°	246.7
37.5°	210.5
40°	171.9
42.5°	134.2
45°	97.1
47.5°	64.0
50°	40.9
52.5°	31.6
55°	28.5
57.5°	26.2
60°	23.9
62.5°	21.6
65°	18.5
67.5°	16.2
70°	13.9
72.5°	11.6
75°	10.0
77.5°	7.7
80°	6.2
82.5°	4.6
85°	2.3
87.5°	1.5
90°	0.0

(END OF REPORT)