

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1299836

Luminaire Tested: P3AS17R25W2N902750DE010 E3DLD1LI\_3000K

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1299836  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-10)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS17R25W2N902750DE010 E3DLD1LI\_3000K  
Description: 3in Adjustable Tunable White LED luminaire with, R25 optic, 3000K CCT AND, 90CRI ,  
E3DLD1LI TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 959.0 lumens  
Efficiency: N/A  
Efficacy: 49.4 lumens/watt  
Spacing Criteria (0/90/45): 0.78 / 0.78 / 0.85  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 19.4  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1299836  
CATALOG NUMBER: P3AS17R25W2N902750DE010 E3DLD1LI\_3000K

### Luminous Intensity Polar Plot





TEST NUMBER: P1299836

CATALOG NUMBER: P3AS17R25W2N902750DE010 E3DLD1LI\_3000K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20					
RC	80				70				50				30				10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	0
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	112	109	106	104	110	107	105	102	103	101	99	99	98	96	96	94	93	91				91
2	106	100	96	92	104	99	94	91	95	92	89	92	89	87	89	87	85	83				83
3	100	92	87	82	98	91	86	82	88	84	80	86	82	79	83	80	78	76				76
4	94	85	79	74	92	84	78	74	82	77	73	80	76	72	78	74	71	70				70
5	89	79	73	68	87	78	72	68	76	71	67	75	70	66	73	69	66	64				64
6	84	74	67	62	82	73	67	62	71	66	62	70	65	61	69	64	61	59				59
7	79	69	62	58	78	68	62	58	67	61	57	66	61	57	65	60	57	55				55
8	75	65	58	54	74	64	58	53	63	57	53	62	57	53	61	56	53	51				51
9	71	61	54	50	70	60	54	50	59	54	50	58	53	50	57	53	49	48				48
10	68	57	51	47	67	57	51	47	56	50	47	55	50	46	54	50	46	45				45

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	227920
5°	222474
10°	206164
15°	183611
20°	157794
25°	134113
30°	110422
35°	86036
40°	61887
45°	39260
50°	23232
55°	15980
60°	14692
65°	13646
70°	12246
75°	11099
80°	10607
85°	9057

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 39260 cd/sqm



TEST NUMBER: P1299836

CATALOG NUMBER: P3AS17R25W2N902750DE010 E3DLD1LI\_3000K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	93.7	9.8
10°-20°	224.5	23.4
20°-30°	253.7	26.5
30°-40°	200.7	20.9
40°-50°	101.4	10.6
50°-60°	40.6	4.2
60°-70°	26.0	2.7
70°-80°	14.3	1.5
80°-90°	4.1	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	572.0	59.6
0°-40°	772.6	80.6
0°-60°	914.6	95.4
0°-90°	959.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	959.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1039	
5°	1011	94
15°	809	225
25°	554	254
35°	321	201
45°	127	101
55°	42	41
65°	26	26
75°	13	14
85°	4	4
90°	0	



TEST NUMBER: P1299836

CATALOG NUMBER: P3AS17R25W2N902750DE010 E3DLD1LI\_3000K

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	1039.4
1°	1039.4
2°	1035.8
3°	1029.8
4°	1021.5
5°	1010.7
6°	997.6
7°	982.1
8°	965.3
9°	946.2
10°	925.9
11°	903.2
12°	881.7
13°	856.6
14°	832.7
15°	808.8
17.5°	741.9
20°	676.2
22.5°	614.1
25°	554.3
27.5°	495.8
30°	436.1
32.5°	379.9
35°	321.4
37.5°	267.6
40°	216.2
42.5°	168.5
45°	126.6
47.5°	94.4
50°	68.1
52.5°	51.4
55°	41.8
57.5°	38.2
60°	33.5
62.5°	29.9
65°	26.3
67.5°	22.7
70°	19.1
72.5°	16.7
75°	13.1
77.5°	10.8
80°	8.4
82.5°	6.0
85°	3.6
87.5°	1.2



TEST NUMBER: P1299836  
CATALOG NUMBER: P3AS17R25W2N902750DE010 E3DLD1LI\_3000K

**CANDELA DISTRIBUTION (continued):**

0°  
90° | 0.0

(END OF REPORT)