

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1299885

Luminaire Tested: P3AS17R25W2N902750DE010 E3PH1MW_2700K

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1299885
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2509-551-3)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R25W2N902750DE010 E3PH1MW_2700K
Description: 3in Adjustable Tunable White LED luminaire with, R25 optic, 2700K CCT AND, 90CRI ,
E3PH1MW TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1151.0 lumens
Efficiency: N/A
Efficacy: 59.3 lumens/watt
Spacing Criteria (0/90/45): 0.36 / 0.36 / 0.36
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 19.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1299885
CATALOG NUMBER: P3AS17R25W2N902750DE010 E3PH1MW_2700K

Luminous Intensity Polar Plot





TEST NUMBER: P1299885
 CATALOG NUMBER: P3AS17R25W2N902750DE010 E3PH1MW_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	116	114	112	111	113	112	110	109	108	107	106	104	103	102	101	100	99	98	98	98	98
2	113	109	107	105	111	108	105	103	105	103	101	102	100	99	99	98	97	96	96	96	96
3	110	106	103	100	108	104	102	99	102	100	98	100	98	96	98	96	95	94	94	94	94
4	107	103	99	97	106	102	99	96	100	97	95	98	96	94	96	95	93	92	92	92	92
5	105	100	96	94	103	99	96	93	97	95	93	96	94	92	95	93	91	90	90	90	90
6	102	97	94	91	101	97	93	91	95	93	91	94	92	90	93	91	89	89	89	89	89
7	100	95	92	89	99	95	91	89	94	91	89	93	90	88	92	89	88	87	87	87	87
8	98	93	90	87	98	93	89	87	92	89	87	91	88	87	90	88	86	85	85	85	85
9	97	91	88	86	96	91	88	85	90	87	85	89	87	85	89	86	85	84	84	84	84
10	95	89	86	84	94	89	86	84	88	86	84	88	85	83	87	85	83	83	83	83	83

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1760385
5°	1503518
10°	947901
15°	441160
20°	90845
25°	18533
30°	3950
35°	830
40°	458
45°	0
50°	0
55°	0
60°	0
65°	0
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 0 cd/sqm



TEST NUMBER: P1299885

CATALOG NUMBER: P3AS17R25W2N902750DE010 E3PH1MW_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	569.2	49.5
10°-20°	528.7	45.9
20°-30°	50.0	4.3
30°-40°	2.9	0.3
40°-50°	0.1	0.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1147.9	99.7
0°-40°	1150.9	100.0
0°-60°	1151.0	100.0
0°-90°	1151.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1151.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	8028	
5°	6830	569
15°	1943	529
25°	77	50
35°	3	3
45°	0	0
55°	0	0
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P1299885
CATALOG NUMBER: P3AS17R25W2N902750DE010 E3PH1MW_2700K

CANDELA DISTRIBUTION (FULL):

	0°
0°	8028.0
2.5°	7729.4
5°	6830.5
7.5°	5615.7
10°	4257.1
12.5°	3075.2
15°	1943.3
17.5°	939.6
20°	389.3
22.5°	154.8
25°	76.6
27.5°	36.0
30°	15.6
32.5°	6.3
35°	3.1
37.5°	1.6
40°	1.6
42.5°	0.0
45°	0.0
47.5°	0.0
50°	0.0
52.5°	0.0
55°	0.0
57.5°	0.0
60°	0.0
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)