

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1299891

Luminaire Tested: P3AS17R25W2N902750DE010 E3PHLD1MW_3000K

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1299891
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2509-551-11)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R25W2N902750DE010 E3PHLD1MW_3000K
Description: 3in Adjustable Tunable White LED luminaire with, R25 optic, 3000K CCT AND, 90CRI ,
E3PHLD1MW TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 959.0 lumens
Efficiency: N/A
Efficacy: 49.4 lumens/watt
Spacing Criteria (0/90/45): 0.62 / 0.62 / 0.71
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 19.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1299891
CATALOG NUMBER: P3AS17R25W2N902750DE010 E3PHLD1MW_3000K

Luminous Intensity Polar Plot





TEST NUMBER: P1299891

CATALOG NUMBER: P3AS17R25W2N902750DE010 E3PHLD1MW_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	112	108	105	102	109	106	103	100	102	99	97	98	96	94	95	93	92	90
2	104	98	93	89	102	96	92	88	93	89	86	90	87	84	87	84	82	80
3	97	89	83	78	95	88	82	77	85	80	76	83	78	75	80	77	74	72
4	91	82	75	70	89	81	74	69	78	73	69	76	72	68	74	70	67	65
5	86	76	68	63	84	75	68	63	73	67	62	71	66	62	69	65	61	59
6	81	70	63	58	79	69	62	57	68	62	57	66	61	57	65	60	56	55
7	76	65	58	53	75	64	58	53	63	57	53	62	56	52	61	56	52	50
8	72	61	54	49	71	60	54	49	59	53	49	58	53	49	57	52	48	47
9	68	57	50	46	67	57	50	46	56	50	46	55	49	45	54	49	45	44
10	65	54	47	43	64	53	47	43	52	47	43	52	46	43	51	46	42	41

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	250221
5°	237530
10°	205719
15°	167492
20°	132335
25°	105514
30°	85557
35°	69680
40°	57737
45°	48656
50°	41176
55°	36242
60°	31752
65°	27707
70°	24299
75°	20418
80°	15280
85°	8554

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 48656 cd/sqm



TEST NUMBER: P1299891

CATALOG NUMBER: P3AS17R25W2N902750DE010 E3PHLD1MW_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	98.0	10.2
10°-20°	204.6	21.3
20°-30°	201.6	21.0
30°-40°	164.2	17.1
40°-50°	121.8	12.7
50°-60°	85.0	8.9
60°-70°	53.2	5.6
70°-80°	25.6	2.7
80°-90°	4.9	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	504.2	52.6
0°-40°	668.4	69.7
0°-60°	875.2	91.3
0°-90°	959.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	959.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1141	
5°	1079	98
15°	738	205
25°	436	202
35°	260	164
45°	157	122
55°	95	85
65°	53	53
75°	24	26
85°	3	5
90°	0	



TEST NUMBER: P1299891

CATALOG NUMBER: P3AS17R25W2N902750DE010 E3PHLD1MW_3000K

CANDELA DISTRIBUTION (FULL):

	0°
0°	1141.1
2.5°	1125.6
5°	1079.1
7.5°	1008.4
10°	923.9
12.5°	830.8
15°	737.8
17.5°	646.4
20°	567.1
22.5°	498.2
25°	436.1
27.5°	382.7
30°	337.9
32.5°	296.5
35°	260.3
37.5°	229.3
40°	201.7
42.5°	177.5
45°	156.9
47.5°	137.9
50°	120.7
52.5°	106.9
55°	94.8
57.5°	82.7
60°	72.4
62.5°	62.1
65°	53.4
67.5°	44.8
70°	37.9
72.5°	31.0
75°	24.1
77.5°	17.2
80°	12.1
82.5°	6.9
85°	3.4
87.5°	1.7
90°	0.0

(END OF REPORT)