

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1297554

Luminaire Tested: P3AS13R50W2N902750DE010 E3CB1MB_4000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1297554
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-32)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R50W2N902750DE010 E3CB1MB_4000K
Description: 3in Adjustable Tunable White LED luminaire with, R50 optic, 4000K CCT AND, 90CRI ,
E3CB1MB TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1062.0 lumens
Efficiency: N/A
Efficacy: 86.3 lumens/watt
Spacing Criteria (0/90/45): 0.84 / 0.84 / 0.76
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 12.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1297554
CATALOG NUMBER: P3AS13R50W2N902750DE010 E3CB1MB_4000K

Luminous Intensity Polar Plot





TEST NUMBER: P1297554

CATALOG NUMBER: P3AS13R50W2N902750DE010 E3CB1MB_4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	154.9	14.6
10°-20°	391.6	36.9
20°-30°	392.2	36.9
30°-40°	110.3	10.4
40°-50°	6.7	0.6
50°-60°	2.5	0.2
60°-70°	2.0	0.2
70°-80°	1.4	0.1
80°-90°	0.5	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	938.7	88.4
0°-40°	1049.0	98.8
0°-60°	1058.1	99.6
0°-90°	1062.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1062.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1687	
5°	1650	155
15°	1409	392
25°	893	392
35°	141	110
45°	4	7
55°	3	3
65°	2	2
75°	2	1
85°	1	1
90°	0	



TEST NUMBER: P1297554
CATALOG NUMBER: P3AS13R50W2N902750DE010 E3CB1MB_4000K

CANDELA DISTRIBUTION (FULL):

	0°
0°	1686.7
2.5°	1678.2
5°	1650.2
7.5°	1612.2
10°	1566.4
12.5°	1497.3
15°	1408.8
17.5°	1307.1
20°	1208.6
22.5°	1085.9
25°	893.4
27.5°	665.2
30°	464.2
32.5°	280.2
35°	141.3
37.5°	66.8
40°	31.0
42.5°	11.6
45°	3.9
47.5°	3.1
50°	3.1
52.5°	3.1
55°	3.1
57.5°	2.3
60°	2.3
62.5°	2.3
65°	2.3
67.5°	1.6
70°	1.6
72.5°	1.6
75°	1.6
77.5°	0.8
80°	0.8
82.5°	0.8
85°	0.8
87.5°	0.0
90°	0.0

(END OF REPORT)