

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1299898

Luminaire Tested: P3AS17R25W2N902750DE010 E3PHLP1MW\_4000K

Issue Date: 1/29/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1299898  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2509-551-7)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/29/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS17R25W2N902750DE010 E3PHLP1MW\_4000K  
Description: 3in Adjustable Tunable White LED luminaire with, R25 optic, 4000K CCT AND, 90CRI ,  
E3PHLP1MW TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 699.1 lumens  
Efficiency: N/A  
Efficacy: 36.0 lumens/watt  
Spacing Criteria (0/90/45): 0.59 / 0.59 / 0.65  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 19.4  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1299898  
CATALOG NUMBER: P3AS17R25W2N902750DE010 E3PHLP1MW\_4000K

### Luminous Intensity Polar Plot







TEST NUMBER: P1299898

CATALOG NUMBER: P3AS17R25W2N902750DE010 E3PHLP1MW\_4000K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	91.0	13.0
10°-20°	182.1	26.1
20°-30°	161.3	23.1
30°-40°	102.7	14.7
40°-50°	54.4	7.8
50°-60°	40.0	5.7
60°-70°	34.0	4.9
70°-80°	24.1	3.4
80°-90°	9.5	1.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	434.4	62.1
0°-40°	537.1	76.8
0°-60°	631.5	90.3
0°-90°	699.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	699.1	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1071	
5°	1008	91
15°	658	182
25°	350	161
35°	163	103
45°	66	54
55°	44	40
65°	35	34
75°	23	24
85°	9	10
90°	0	



TEST NUMBER: P1299898

CATALOG NUMBER: P3AS17R25W2N902750DE010 E3PHLP1MW\_4000K

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	1071.1
2.5°	1055.3
5°	1008.1
7.5°	934.6
10°	847.1
12.5°	752.5
15°	658.0
17.5°	567.0
20°	486.5
22.5°	413.0
25°	350.0
27.5°	294.0
30°	243.3
32.5°	199.5
35°	162.8
37.5°	129.5
40°	103.3
42.5°	82.3
45°	66.5
47.5°	57.8
50°	50.8
52.5°	47.3
55°	43.8
57.5°	42.0
60°	40.3
62.5°	36.8
65°	35.0
67.5°	31.5
70°	28.0
72.5°	26.3
75°	22.8
77.5°	19.3
80°	17.5
82.5°	14.0
85°	8.8
87.5°	3.5
90°	0.0

(END OF REPORT)