

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1297573

Luminaire Tested: P3AS13R50W2N902750DE010 E3CD1MMS\_3500K

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1297573  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-32)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS13R50W2N902750DE010 E3CD1MMS\_3500K  
Description: 3in Adjustable Tunable White LED luminaire with, R50 optic, 3500K CCT AND, 90CRI ,  
E3CD1MMS TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1062.0 lumens  
Efficiency: N/A  
Efficacy: 86.3 lumens/watt  
Spacing Criteria (0/90/45): 0.84 / 0.84 / 0.76  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 12.3  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1297573  
CATALOG NUMBER: P3AS13R50W2N902750DE010 E3CD1MMS\_3500K

### Luminous Intensity Polar Plot





TEST NUMBER: P1297573  
 CATALOG NUMBER: P3AS13R50W2N902750DE010 E3CD1MMS\_3500K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	114	112	109	107	112	109	107	106	105	104	102	102	101	99	98	97	96	95	95	95	95
2	109	105	101	98	107	103	100	97	100	97	95	97	95	93	94	93	91	90	90	90	90
3	105	99	95	91	103	98	94	90	95	92	89	93	90	88	91	88	86	85	85	85	85
4	100	94	89	85	99	92	88	85	90	87	84	88	85	83	87	84	82	80	80	80	80
5	96	89	84	80	94	88	83	79	86	82	79	84	81	78	83	80	77	76	76	76	76
6	92	84	79	75	91	83	79	75	82	78	74	81	77	74	79	76	73	72	72	72	72
7	88	80	75	71	87	79	74	71	78	74	71	77	73	70	76	73	70	69	69	69	69
8	85	76	71	67	83	76	71	67	75	70	67	74	70	67	73	69	66	65	65	65	65
9	81	73	68	64	80	72	67	64	71	67	64	71	66	63	70	66	63	62	62	62	62
10	78	69	64	61	77	69	64	61	68	64	61	68	63	61	67	63	60	59	59	59	59

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	369861
5°	363239
10°	348780
15°	319820
20°	282031
25°	216158
30°	117537
35°	37825
40°	8874
45°	1209
50°	1058
55°	1185
60°	1009
65°	1193
70°	1026
75°	1356
80°	1010
85°	2013

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 85°  
 Luminance: 2013 cd/sqm



TEST NUMBER: P1297573

CATALOG NUMBER: P3AS13R50W2N902750DE010 E3CD1MMS\_3500K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	154.9	14.6
10°-20°	391.6	36.9
20°-30°	392.2	36.9
30°-40°	110.3	10.4
40°-50°	6.7	0.6
50°-60°	2.5	0.2
60°-70°	2.0	0.2
70°-80°	1.4	0.1
80°-90°	0.5	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	938.7	88.4
0°-40°	1049.0	98.8
0°-60°	1058.1	99.6
0°-90°	1062.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1062.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1687	
5°	1650	155
15°	1409	392
25°	893	392
35°	141	110
45°	4	7
55°	3	3
65°	2	2
75°	2	1
85°	1	1
90°	0	



TEST NUMBER: P1297573  
CATALOG NUMBER: P3AS13R50W2N902750DE010 E3CD1MMS\_3500K

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	1686.7
2.5°	1678.2
5°	1650.2
7.5°	1612.2
10°	1566.4
12.5°	1497.3
15°	1408.8
17.5°	1307.1
20°	1208.6
22.5°	1085.9
25°	893.4
27.5°	665.2
30°	464.2
32.5°	280.2
35°	141.3
37.5°	66.8
40°	31.0
42.5°	11.6
45°	3.9
47.5°	3.1
50°	3.1
52.5°	3.1
55°	3.1
57.5°	2.3
60°	2.3
62.5°	2.3
65°	2.3
67.5°	1.6
70°	1.6
72.5°	1.6
75°	1.6
77.5°	0.8
80°	0.8
82.5°	0.8
85°	0.8
87.5°	0.0
90°	0.0

(END OF REPORT)