

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1297582

Luminaire Tested: P3AS13R50W2N902750DE010 E3D1H\_3000K

Issue Date: 1/29/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1297582  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-13)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/29/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS13R50W2N902750DE010 E3D1H\_3000K  
Description: 3in Adjustable Tunable White LED luminaire with, R50 optic, 3000K CCT AND, 90CRI , E3D1H TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1062.0 lumens  
Efficiency: N/A  
Efficacy: 86.3 lumens/watt  
Spacing Criteria (0/90/45): 0.82 / 0.82 / 0.77  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 12.3  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1297582  
CATALOG NUMBER: P3AS13R50W2N902750DE010 E3D1H\_3000K

### Luminous Intensity Polar Plot







TEST NUMBER: P1297582

CATALOG NUMBER: P3AS13R50W2N902750DE010 E3D1H\_3000K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	153.7	14.5
10°-20°	380.9	35.9
20°-30°	400.4	37.7
30°-40°	114.6	10.8
40°-50°	11.2	1.1
50°-60°	0.9	0.1
60°-70°	0.3	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	935.0	88.0
0°-40°	1049.6	98.8
0°-60°	1061.6	100.0
0°-90°	1062.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1062.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1692	
5°	1641	154
15°	1375	381
25°	915	400
35°	148	115
45°	12	11
55°	1	1
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P1297582

CATALOG NUMBER: P3AS13R50W2N902750DE010 E3D1H\_3000K

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	1692.5
1°	1689.9
2°	1682.4
3°	1671.5
4°	1656.9
5°	1641.1
6°	1624.3
7°	1606.3
8°	1589.4
9°	1569.9
10°	1548.2
11°	1523.1
12°	1494.3
13°	1458.3
14°	1419.3
15°	1374.7
16°	1327.5
17°	1281.8
18°	1235.0
19°	1193.8
20°	1157.0
21°	1121.8
22°	1081.7
23°	1035.6
24°	981.7
25°	915.4
26°	843.4
27°	763.2
28°	683.4
29°	597.3
30°	502.5
31°	413.7
32°	332.0
32.5°	296.4
33°	260.4
34°	199.7
35°	147.6
36°	108.3
37°	80.6
37.5°	69.7
38°	60.3
39°	46.8
40°	37.1
42.5°	21.0
45°	12.0



TEST NUMBER: P1297582

CATALOG NUMBER: P3AS13R50W2N902750DE010 E3D1H\_3000K

**CANDELA DISTRIBUTION (continued):**

	0°
47.5°	6.7
50°	2.6
52.5°	1.1
55°	0.7
57.5°	0.7
60°	0.4
62.5°	0.4
65°	0.4
67.5°	0.4
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)