

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1297592

Luminaire Tested: P3AS13R50W2N902750DE010 E3D1MW_3000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1297592
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-32)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R50W2N902750DE010 E3D1MW_3000K
Description: 3in Adjustable Tunable White LED luminaire with, R50 optic, 3000K CCT AND, 90CRI , E3D1MW TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1046.1 lumens
Efficiency: N/A
Efficacy: 85.0 lumens/watt
Spacing Criteria (0/90/45): 0.84 / 0.84 / 0.76
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 12.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1297592
CATALOG NUMBER: P3AS13R50W2N902750DE010 E3D1MW_3000K

Luminous Intensity Polar Plot





TEST NUMBER: P1297592

CATALOG NUMBER: P3AS13R50W2N902750DE010 E3D1MW_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	152.5	14.6
10°-20°	385.7	36.9
20°-30°	386.3	36.9
30°-40°	108.6	10.4
40°-50°	6.6	0.6
50°-60°	2.5	0.2
60°-70°	2.0	0.2
70°-80°	1.3	0.1
80°-90°	0.5	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	924.5	88.4
0°-40°	1033.2	98.8
0°-60°	1042.2	99.6
0°-90°	1046.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1046.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1661	
5°	1625	153
15°	1388	386
25°	880	386
35°	139	109
45°	4	7
55°	3	3
65°	2	2
75°	2	1
85°	1	1
90°	0	



TEST NUMBER: P1297592

CATALOG NUMBER: P3AS13R50W2N902750DE010 E3D1MW_3000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	1661.3
2.5°	1652.9
5°	1625.4
7.5°	1587.9
10°	1542.8
12.5°	1474.8
15°	1387.6
17.5°	1287.4
20°	1190.4
22.5°	1069.6
25°	880.0
27.5°	655.2
30°	457.2
32.5°	276.0
35°	139.1
37.5°	65.7
40°	30.6
42.5°	11.5
45°	3.8
47.5°	3.1
50°	3.1
52.5°	3.1
55°	3.1
57.5°	2.3
60°	2.3
62.5°	2.3
65°	2.3
67.5°	1.5
70°	1.5
72.5°	1.5
75°	1.5
77.5°	0.8
80°	0.8
82.5°	0.8
85°	0.8
87.5°	0.0
90°	0.0

(END OF REPORT)