

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1299913

Luminaire Tested: P3AS17R25W2N902765DE010 E3CB1MW_3000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1299913
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-12)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R25W2N902765DE010 E3CB1MW_3000K
Description: 3in Adjustable Tunable White LED luminaire with, R25 optic, 3000K CCT AND, 90CRI ,
E3CB1MW TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1520.0 lumens
Efficiency: N/A
Efficacy: 78.4 lumens/watt
Spacing Criteria (0/90/45): 0.45 / 0.45 / 0.41
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 19.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1299913
CATALOG NUMBER: P3AS17R25W2N902765DE010 E3CB1MW_3000K

Luminous Intensity Polar Plot





TEST NUMBER: P1299913

CATALOG NUMBER: P3AS17R25W2N902765DE010 E3CB1MW_3000K

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10° | 602.3 | 39.6 |
| 10°-20° | 718.5 | 47.3 |
| 20°-30° | 162.0 | 10.7 |
| 30°-40° | 26.2 | 1.7 |
| 40°-50° | 4.8 | 0.3 |
| 50°-60° | 2.5 | 0.2 |
| 60°-70° | 2.2 | 0.1 |
| 70°-80° | 1.3 | 0.1 |
| 80°-90° | 0.2 | 0.0 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-30° | 1482.8 | 97.6 |
| 0°-40° | 1509.1 | 99.3 |
| 0°-60° | 1516.4 | 99.8 |
| 0°-90° | 1520.0 | 100.0 |
| 90°-120° | 0.0 | 0.0 |
| 90°-150° | 0.0 | 0.0 |
| 90°-180° | 0.0 | 0.0 |
| 0°-180° | 1520.0 | 100.0 |

CANDELA DISTRIBUTION:

| | 0° | Flux |
|-----|------|------|
| 0° | 7411 | |
| 5° | 6847 | 602 |
| 15° | 2582 | 719 |
| 25° | 316 | 162 |
| 35° | 31 | 26 |
| 45° | 5 | 5 |
| 55° | 2 | 3 |
| 65° | 2 | 2 |
| 75° | 1 | 1 |
| 85° | 0 | 0 |
| 90° | 0 | |



TEST NUMBER: P1299913

CATALOG NUMBER: P3AS17R25W2N902765DE010 E3CB1MW_3000K

CANDELA DISTRIBUTION (FULL):

| 0° | |
|-------|--------|
| 0° | 7411.1 |
| 1° | 7399.1 |
| 2° | 7339.4 |
| 3° | 7229.5 |
| 4° | 7063.5 |
| 5° | 6847.4 |
| 6° | 6589.5 |
| 7° | 6310.0 |
| 8° | 5990.0 |
| 9° | 5640.1 |
| 10° | 5249.6 |
| 11° | 4799.4 |
| 12° | 4281.1 |
| 13° | 3739.0 |
| 14° | 3157.4 |
| 15° | 2581.8 |
| 17.5° | 1471.2 |
| 20° | 825.2 |
| 22.5° | 498.0 |
| 25° | 316.5 |
| 27.5° | 194.7 |
| 30° | 113.4 |
| 32.5° | 59.7 |
| 35° | 31.0 |
| 37.5° | 20.3 |
| 40° | 13.1 |
| 42.5° | 8.4 |
| 45° | 4.8 |
| 47.5° | 3.6 |
| 50° | 3.6 |
| 52.5° | 3.6 |
| 55° | 2.4 |
| 57.5° | 2.4 |
| 60° | 2.4 |
| 62.5° | 2.4 |
| 65° | 2.4 |
| 67.5° | 2.4 |
| 70° | 1.2 |
| 72.5° | 1.2 |
| 75° | 1.2 |
| 77.5° | 1.2 |
| 80° | 1.2 |
| 82.5° | 0.0 |
| 85° | 0.0 |
| 87.5° | 0.0 |



TEST NUMBER: P1299913
CATALOG NUMBER: P3AS17R25W2N902765DE010 E3CB1MW_3000K

CANDELA DISTRIBUTION (continued):



(END OF REPORT)