

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1297602

Luminaire Tested: P3AS13R50W2N902750DE010 E3D1WMH_3000K

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1297602
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-13)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R50W2N902750DE010 E3D1WMH_3000K
Description: 3in Adjustable Tunable White LED luminaire with, R50 optic, 3000K CCT AND, 90CRI ,
E3D1WMH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1062.0 lumens
Efficiency: N/A
Efficacy: 86.3 lumens/watt
Spacing Criteria (0/90/45): 0.82 / 0.82 / 0.77
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 12.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1297602
CATALOG NUMBER: P3AS13R50W2N902750DE010 E3D1WMH_3000K

Luminous Intensity Polar Plot





TEST NUMBER: P1297602

CATALOG NUMBER: P3AS13R50W2N902750DE010 E3D1WMH_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	102	102	102	100
1	114	112	109	107	112	110	108	106	105	104	102	102	101	99	98	97	97	97	97	97	95
2	109	105	101	98	107	103	100	97	100	97	95	97	95	93	94	93	91	94	93	91	90
3	105	99	95	91	103	98	94	90	95	92	89	93	90	88	91	88	86	91	88	86	85
4	100	94	89	85	99	92	88	85	90	87	84	88	85	83	87	84	82	87	84	82	80
5	96	89	84	80	94	88	83	79	86	82	79	84	81	78	83	80	77	83	80	77	76
6	92	84	79	75	91	83	78	75	82	78	74	81	77	74	79	76	73	79	76	73	72
7	88	80	75	71	87	79	74	71	78	74	70	77	73	70	76	72	70	76	72	70	68
8	84	76	71	67	83	76	71	67	75	70	67	74	69	66	73	69	66	73	69	66	65
9	81	73	67	64	80	72	67	64	71	67	63	70	66	63	70	66	63	70	66	63	62
10	78	69	64	61	77	69	64	61	68	64	60	67	63	60	67	63	60	67	63	60	59

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	371133
5°	361236
10°	344728
15°	312079
20°	269990
25°	221481
30°	127235
35°	39511
40°	10620
45°	3721
50°	887
55°	268
60°	175
65°	208
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 3721 cd/sqm



TEST NUMBER: P1297602

CATALOG NUMBER: P3AS13R50W2N902750DE010 E3D1WMH_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	153.7	14.5
10°-20°	380.9	35.9
20°-30°	400.4	37.7
30°-40°	114.6	10.8
40°-50°	11.2	1.1
50°-60°	0.9	0.1
60°-70°	0.3	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	935.0	88.0
0°-40°	1049.6	98.8
0°-60°	1061.6	100.0
0°-90°	1062.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1062.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1692	
5°	1641	154
15°	1375	381
25°	915	400
35°	148	115
45°	12	11
55°	1	1
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P1297602
CATALOG NUMBER: P3AS13R50W2N902750DE010 E3D1WMH_3000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	1692.5
1°	1689.9
2°	1682.4
3°	1671.5
4°	1656.9
5°	1641.1
6°	1624.3
7°	1606.3
8°	1589.4
9°	1569.9
10°	1548.2
11°	1523.1
12°	1494.3
13°	1458.3
14°	1419.3
15°	1374.7
16°	1327.5
17°	1281.8
18°	1235.0
19°	1193.8
20°	1157.0
21°	1121.8
22°	1081.7
23°	1035.6
24°	981.7
25°	915.4
26°	843.4
27°	763.2
28°	683.4
29°	597.3
30°	502.5
31°	413.7
32°	332.0
32.5°	296.4
33°	260.4
34°	199.7
35°	147.6
36°	108.3
37°	80.6
37.5°	69.7
38°	60.3
39°	46.8
40°	37.1
42.5°	21.0
45°	12.0



TEST NUMBER: P1297602
CATALOG NUMBER: P3AS13R50W2N902750DE010 E3D1WMH_3000K

CANDELA DISTRIBUTION (continued):

	0°
47.5°	6.7
50°	2.6
52.5°	1.1
55°	0.7
57.5°	0.7
60°	0.4
62.5°	0.4
65°	0.4
67.5°	0.4
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)