

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1297632

Luminaire Tested: P3AS13R50W2N902750DE010 E3DL1WMH_3000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1297632
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-31)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R50W2N902750DE010 E3DL1WMH_3000K
Description: 3in Adjustable Tunable White LED luminaire with, R50 optic, 3000K CCT AND, 90CRI ,
E3DL1WMH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 860.0 lumens
Efficiency: N/A
Efficacy: 69.9 lumens/watt
Spacing Criteria (0/90/45): 0.77 / 0.77 / 0.75
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 12.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1297632
CATALOG NUMBER: P3AS13R50W2N902750DE010 E3DL1WMH_3000K

Luminous Intensity Polar Plot





TEST NUMBER: P1297632
 CATALOG NUMBER: P3AS13R50W2N902750DE010 E3DL1WMH_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	114	111	108	106	111	109	106	104	105	103	101	101	99	98	97	96	95	94	94	94	94
2	108	103	99	96	106	102	98	95	98	95	93	95	93	91	93	91	89	87	87	87	87
3	103	97	92	88	101	95	91	87	93	89	86	90	87	84	88	85	83	82	82	82	82
4	98	91	85	81	96	90	85	81	87	83	80	85	82	79	84	80	78	76	76	76	76
5	93	85	80	75	92	84	79	75	83	78	74	81	77	74	79	76	73	72	72	72	72
6	89	80	75	71	88	80	74	70	78	73	70	77	73	69	75	72	69	67	67	67	67
7	85	76	70	66	84	75	70	66	74	69	66	73	69	65	72	68	65	64	64	64	64
8	81	72	66	62	80	71	66	62	70	65	62	69	65	62	68	64	61	60	60	60	60
9	78	68	63	59	76	68	62	59	67	62	59	66	62	58	65	61	58	57	57	57	57
10	74	65	59	56	73	65	59	56	64	59	55	63	58	55	62	58	55	54	54	54	54

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	273816
5°	268280
10°	251298
15°	224973
20°	189320
25°	144492
30°	93913
35°	55680
40°	32175
45°	16126
50°	6004
55°	4664
60°	4342
65°	3943
70°	3911
75°	3897
80°	3915
85°	3774

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 16126 cd/sqm



TEST NUMBER: P1297632

CATALOG NUMBER: P3AS13R50W2N902750DE010 E3DL1WMH_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	113.4	13.2
10°-20°	274.1	31.9
20°-30°	268.9	31.3
30°-40°	135.5	15.8
40°-50°	42.8	5.0
50°-60°	11.1	1.3
60°-70°	7.8	0.9
70°-80°	4.9	0.6
80°-90°	1.7	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	656.3	76.3
0°-40°	791.8	92.1
0°-60°	845.6	98.3
0°-90°	860.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	860.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1249	
5°	1219	113
15°	991	274
25°	597	269
35°	208	135
45°	52	43
55°	12	11
65°	8	8
75°	5	5
85°	2	2
90°	0	



TEST NUMBER: P1297632
CATALOG NUMBER: P3AS13R50W2N902750DE010 E3DL1WMH_3000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	1248.7
2.5°	1241.0
5°	1218.8
7.5°	1179.1
10°	1128.6
12.5°	1063.6
15°	991.0
17.5°	906.9
20°	811.3
22.5°	708.1
25°	597.2
27.5°	479.4
30°	370.9
32.5°	279.1
35°	208.0
37.5°	153.7
40°	112.4
42.5°	79.5
45°	52.0
47.5°	29.8
50°	17.6
52.5°	13.0
55°	12.2
57.5°	10.7
60°	9.9
62.5°	9.2
65°	7.6
67.5°	6.9
70°	6.1
72.5°	5.4
75°	4.6
77.5°	3.8
80°	3.1
82.5°	2.3
85°	1.5
87.5°	0.8
90°	0.0

(END OF REPORT)