

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1297653

Luminaire Tested: P3AS13R50W2N902750DE010 E3DLD1MW_3500K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1297653
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-30)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R50W2N902750DE010 E3DLD1MW_3500K
Description: 3in Adjustable Tunable White LED luminaire with, R50 optic, 3500K CCT AND, 90CRI ,
E3DLD1MW TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 680.0 lumens
Efficiency: N/A
Efficacy: 55.3 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.93
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 12.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1297653
CATALOG NUMBER: P3AS13R50W2N902750DE010 E3DLD1MW_3500K

Luminous Intensity Polar Plot





TEST NUMBER: P1297653

CATALOG NUMBER: P3AS13R50W2N902750DE010 E3DLD1MW_3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	58.0	8.5
10°-20°	148.0	21.8
20°-30°	179.8	26.4
30°-40°	152.5	22.4
40°-50°	79.2	11.6
50°-60°	28.5	4.2
60°-70°	19.8	2.9
70°-80°	10.7	1.6
80°-90°	3.4	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	385.8	56.7
0°-40°	538.3	79.2
0°-60°	646.1	95.0
0°-90°	680.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	680.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	630	
5°	619	58
15°	531	148
25°	394	180
35°	245	153
45°	102	79
55°	31	29
65°	20	20
75°	10	11
85°	3	3
90°	0	



TEST NUMBER: P1297653
CATALOG NUMBER: P3AS13R50W2N902750DE010 E3DLD1MW_3500K

CANDELA DISTRIBUTION (FULL):

	0°
0°	630.2
2.5°	627.9
5°	618.6
7.5°	604.6
10°	584.4
12.5°	558.8
15°	530.9
17.5°	499.0
20°	464.1
22.5°	428.4
25°	393.5
27.5°	357.0
30°	319.8
32.5°	282.5
35°	245.2
37.5°	208.8
40°	172.3
42.5°	137.4
45°	102.4
47.5°	68.3
50°	44.2
52.5°	34.1
55°	31.0
57.5°	27.9
60°	25.6
62.5°	22.5
65°	20.2
67.5°	17.1
70°	14.7
72.5°	12.4
75°	10.1
77.5°	7.8
80°	6.2
82.5°	4.7
85°	3.1
87.5°	1.6
90°	0.0

(END OF REPORT)