

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1300207

Luminaire Tested: P3AS17R30W2N902750DE010 E3DLP1GPH\_2700K

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1300207  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-13)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS17R30W2N902750DE010 E3DLP1GPH\_2700K  
Description: 3in Adjustable Tunable White LED luminaire with, R30 optic, 2700K CCT AND, 90CRI ,  
E3DLP1GPH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 342.0 lumens  
Efficiency: N/A  
Efficacy: 17.6 lumens/watt  
Spacing Criteria (0/90/45): 0.66 / 0.66 / 0.7  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 19.4  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1300207  
CATALOG NUMBER: P3AS17R30W2N902750DE010 E3DLP1GPH\_2700K

### Luminous Intensity Polar Plot





TEST NUMBER: P1300207

CATALOG NUMBER: P3AS17R30W2N902750DE010 E3DLP1GPH\_2700K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93	93	93	93
2	107	102	98	95	105	101	97	94	97	94	92	94	92	90	92	90	88	86	86	86	86
3	102	95	90	86	100	94	89	85	91	87	84	89	86	83	87	84	82	80	80	80	80
4	97	89	84	79	95	88	83	79	86	81	78	84	80	77	82	79	76	74	74	74	74
5	92	84	78	73	90	83	77	73	81	76	72	79	75	72	78	74	71	70	70	70	70
6	88	79	73	68	86	78	72	68	76	71	68	75	71	67	74	70	67	65	65	65	65
7	83	74	68	64	82	74	68	64	72	67	63	71	67	63	70	66	63	61	61	61	61
8	80	70	64	60	78	70	64	60	69	63	60	67	63	60	67	62	59	58	58	58	58
9	76	67	61	57	75	66	60	57	65	60	56	64	60	56	63	59	56	55	55	55	55
10	73	63	58	54	72	63	57	54	62	57	53	61	57	53	61	56	53	52	52	52	52

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	116877
5°	113229
10°	102024
15°	84382
20°	65339
25°	49019
30°	35575
35°	23718
40°	14570
45°	8559
50°	5254
55°	4244
60°	3728
65°	3009
70°	2693
75°	2711
80°	2020
85°	2768

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 8559 cd/sqm



TEST NUMBER: P1300207

CATALOG NUMBER: P3AS17R30W2N902750DE010 E3DLP1GPH\_2700K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	47.3	13.8
10°-20°	102.4	29.9
20°-30°	93.1	27.2
30°-40°	56.3	16.5
40°-50°	22.6	6.6
50°-60°	10.0	2.9
60°-70°	6.0	1.8
70°-80°	3.3	1.0
80°-90°	1.0	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	242.8	71.0
0°-40°	299.2	87.5
0°-60°	331.7	97.0
0°-90°	342.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	342.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	533	
5°	514	47
15°	372	102
25°	203	93
35°	89	56
45°	28	23
55°	11	10
65°	6	6
75°	3	3
85°	1	1
90°	0	



TEST NUMBER: P1300207  
CATALOG NUMBER: P3AS17R30W2N902750DE010 E3DLP1GPH\_2700K

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	533.0
1°	532.4
2°	530.3
3°	526.6
4°	521.3
5°	514.4
6°	505.9
7°	496.9
8°	485.2
9°	472.0
10°	458.2
11°	442.3
12°	425.3
13°	408.3
14°	389.8
15°	371.7
17.5°	324.5
20°	280.0
22.5°	238.6
25°	202.6
27.5°	169.7
30°	140.5
32.5°	113.5
35°	88.6
37.5°	67.9
40°	50.9
42.5°	37.1
45°	27.6
47.5°	20.7
50°	15.4
52.5°	12.2
55°	11.1
57.5°	9.5
60°	8.5
62.5°	6.9
65°	5.8
67.5°	5.3
70°	4.2
72.5°	3.7
75°	3.2
77.5°	2.7
80°	1.6
82.5°	1.1
85°	1.1
87.5°	0.5



TEST NUMBER: P1300207  
CATALOG NUMBER: P3AS17R30W2N902750DE010 E3DLP1GPH\_2700K

CANDELA DISTRIBUTION (continued):

0°  
90° | 0.0

(END OF REPORT)