

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1297834

Luminaire Tested: P3AS13R50W2N902765DE010 E3DLP1GPH_2700K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1297834
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-29)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R50W2N902765DE010 E3DLP1GPH_2700K
Description: 3in Adjustable Tunable White LED luminaire with, R50 optic, 2700K CCT AND, 90CRI ,
E3DLP1GPH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 251.0 lumens
Efficiency: N/A
Efficacy: 20.4 lumens/watt
Spacing Criteria (0/90/45): 0.75 / 0.75 / 0.77
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 12.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1297834
CATALOG NUMBER: P3AS13R50W2N902765DE010 E3DLP1GPH_2700K

Luminous Intensity Polar Plot





TEST NUMBER: P1297834
 CATALOG NUMBER: P3AS13R50W2N902765DE010 E3DLP1GPH_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	113	110	107	105	111	108	106	103	104	102	100	100	99	97	97	95	94	93			93
2	107	102	98	94	105	100	96	93	97	94	91	94	91	89	91	89	87	85			85
3	101	95	89	85	99	93	88	85	91	87	83	88	85	82	86	83	81	79			79
4	96	88	82	78	94	87	82	78	85	80	77	83	79	76	81	78	75	73			73
5	91	83	76	72	90	82	76	72	80	75	71	78	74	70	77	73	70	68			68
6	87	77	71	67	85	77	71	67	75	70	66	74	69	66	72	68	65	64			64
7	82	73	67	62	81	72	66	62	71	66	62	70	65	61	68	64	61	60			60
8	78	69	63	58	77	68	62	58	67	62	58	66	61	58	65	61	57	56			56
9	75	65	59	55	74	64	59	55	63	58	55	63	58	54	62	57	54	53			53
10	71	61	56	52	70	61	55	52	60	55	51	59	55	51	59	54	51	50			50

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	72999
5°	71032
10°	65508
15°	57617
20°	48188
25°	38228
30°	28030
35°	19274
40°	12252
45°	6853
50°	3718
55°	3135
60°	2675
65°	2491
70°	2180
75°	2033
80°	1768
85°	1761

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 6853 cd/sqm



TEST NUMBER: P1297834

CATALOG NUMBER: P3AS13R50W2N902765DE010 E3DLP1GPH_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	29.9	11.9
10°-20°	70.3	28.0
20°-30°	71.9	28.6
30°-40°	45.6	18.2
40°-50°	18.1	7.2
50°-60°	7.4	2.9
60°-70°	4.7	1.9
70°-80°	2.4	1.0
80°-90°	0.7	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	172.1	68.5
0°-40°	217.6	86.7
0°-60°	243.1	96.9
0°-90°	251.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	251.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	333	
5°	323	30
15°	254	70
25°	158	72
35°	72	46
45°	22	18
55°	8	7
65°	5	5
75°	2	2
85°	1	1
90°	0	



TEST NUMBER: P1297834
CATALOG NUMBER: P3AS13R50W2N902765DE010 E3DLP1GPH_2700K

CANDELA DISTRIBUTION (FULL):

	0°
0°	332.9
2.5°	330.5
5°	322.7
7.5°	310.5
10°	294.2
12.5°	274.8
15°	253.8
17.5°	230.7
20°	206.5
22.5°	182.4
25°	158.0
27.5°	133.5
30°	110.7
32.5°	90.4
35°	72.0
37.5°	56.4
40°	42.8
42.5°	31.6
45°	22.1
47.5°	14.9
50°	10.9
52.5°	9.2
55°	8.2
57.5°	7.1
60°	6.1
62.5°	5.4
65°	4.8
67.5°	4.1
70°	3.4
72.5°	2.7
75°	2.4
77.5°	1.7
80°	1.4
82.5°	1.0
85°	0.7
87.5°	0.3
90°	0.0

(END OF REPORT)