

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1300243

Luminaire Tested: P3AS17R30W2N902750DE010 E3PHLD1MW_3000K

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1300243
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2509-551-12)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R30W2N902750DE010 E3PHLD1MW_3000K
Description: 3in Adjustable Tunable White LED luminaire with, R30 optic, 3000K CCT AND, 90CRI ,
E3PHLD1MW TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 929.0 lumens
Efficiency: N/A
Efficacy: 47.9 lumens/watt
Spacing Criteria (0/90/45): 0.65 / 0.65 / 0.74
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 19.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1300243
CATALOG NUMBER: P3AS17R30W2N902750DE010 E3PHLD1MW_3000K

Luminous Intensity Polar Plot





TEST NUMBER: P1300243

CATALOG NUMBER: P3AS17R30W2N902750DE010 E3PHLD1MW_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	112	108	105	102	109	106	103	100	102	99	97	98	96	94	94	93	91	90
2	104	98	93	88	102	96	91	87	93	89	85	90	86	83	87	84	82	80
3	97	89	83	78	95	88	82	77	85	80	76	82	78	75	80	76	73	71
4	91	82	75	69	89	80	74	69	78	72	68	76	71	67	74	70	66	65
5	85	75	68	63	84	74	67	62	72	66	62	70	65	61	69	64	61	59
6	80	69	62	57	79	69	62	57	67	61	56	65	60	56	64	59	56	54
7	76	65	57	52	74	64	57	52	62	56	52	61	56	52	60	55	51	50
8	71	60	53	48	70	60	53	48	58	52	48	57	52	48	56	51	48	46
9	68	57	50	45	66	56	49	45	55	49	45	54	49	45	53	48	44	43
10	64	53	47	42	63	53	46	42	52	46	42	51	46	42	50	45	42	40

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	228929
5°	218798
10°	188730
15°	156437
20°	128228
25°	103361
30°	83304
35°	68262
40°	56706
45°	48067
50°	41142
55°	35554
60°	31752
65°	27707
70°	24299
75°	20418
80°	15280
85°	8554

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 48067 cd/sqm



TEST NUMBER: P1300243

CATALOG NUMBER: P3AS17R30W2N902750DE010 E3PHLD1MW_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	90.1	9.7
10°-20°	192.2	20.7
20°-30°	196.9	21.2
30°-40°	161.0	17.3
40°-50°	120.4	13.0
50°-60°	84.6	9.1
60°-70°	53.2	5.7
70°-80°	25.6	2.8
80°-90°	4.9	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	479.2	51.6
0°-40°	640.2	68.9
0°-60°	845.2	91.0
0°-90°	929.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	929.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1044	
5°	994	90
15°	689	192
25°	427	197
35°	255	161
45°	155	120
55°	93	85
65°	53	53
75°	24	26
85°	3	5
90°	0	



TEST NUMBER: P1300243

CATALOG NUMBER: P3AS17R30W2N902750DE010 E3PHLD1MW_3000K

CANDELA DISTRIBUTION (FULL):

	0°
0°	1044.0
2.5°	1033.6
5°	994.0
7.5°	928.5
10°	847.6
12.5°	768.3
15°	689.1
17.5°	616.7
20°	549.5
22.5°	485.8
25°	427.2
27.5°	375.5
30°	329.0
32.5°	291.1
35°	255.0
37.5°	225.7
40°	198.1
42.5°	175.7
45°	155.0
47.5°	136.1
50°	120.6
52.5°	106.8
55°	93.0
57.5°	82.7
60°	72.4
62.5°	62.0
65°	53.4
67.5°	44.8
70°	37.9
72.5°	31.0
75°	24.1
77.5°	17.2
80°	12.1
82.5°	6.9
85°	3.4
87.5°	1.7
90°	0.0

(END OF REPORT)