

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1300347

Luminaire Tested: P3AS17R30W2N902765DE010 E3DL1WH_6500K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1300347
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-13)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R30W2N902765DE010 E3DL1WH_6500K
Description: 3in Adjustable Tunable White LED luminaire with, R30 optic, 6500K CCT AND, 90CRI ,
E3DL1WH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 777.0 lumens
Efficiency: N/A
Efficacy: 40.0 lumens/watt
Spacing Criteria (0/90/45): 0.66 / 0.66 / 0.7
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 19.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1300347
CATALOG NUMBER: P3AS17R30W2N902765DE010 E3DL1WH_6500K

Luminous Intensity Polar Plot





TEST NUMBER: P1300347

CATALOG NUMBER: P3AS17R30W2N902765DE010 E3DL1WH_6500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93	93	93	93
2	107	102	98	95	105	101	97	94	97	94	92	94	92	90	92	90	88	86	86	86	86
3	102	95	90	86	100	94	89	85	91	87	84	89	86	83	87	84	82	80	80	80	80
4	97	89	84	79	95	88	83	79	86	81	78	84	80	77	82	79	76	74	74	74	74
5	92	84	78	73	90	83	77	73	81	76	72	79	75	72	78	74	71	70	70	70	70
6	88	79	73	68	86	78	72	68	76	71	68	75	71	67	74	70	67	65	65	65	65
7	83	74	68	64	82	74	68	64	72	67	63	71	67	63	70	66	63	61	61	61	61
8	80	70	64	60	78	70	64	60	69	63	60	67	63	60	67	62	59	58	58	58	58
9	76	67	61	57	75	66	60	57	65	60	56	64	60	56	63	59	56	55	55	55	55
10	73	63	58	54	72	63	57	54	62	57	54	61	57	53	61	56	53	52	52	52	52

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	265505
5°	257252
10°	231793
15°	191738
20°	148436
25°	111345
30°	80848
35°	53860
40°	33119
45°	19444
50°	11906
55°	9672
60°	8464
65°	6901
70°	6155
75°	6100
80°	4546
85°	6038

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 19444 cd/sqm



TEST NUMBER: P1300347

CATALOG NUMBER: P3AS17R30W2N902765DE010 E3DL1WH_6500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	107.5	13.8
10°-20°	232.6	29.9
20°-30°	211.6	27.2
30°-40°	127.9	16.5
40°-50°	51.3	6.6
50°-60°	22.7	2.9
60°-70°	13.7	1.8
70°-80°	7.4	1.0
80°-90°	2.1	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	551.7	71.0
0°-40°	679.7	87.5
0°-60°	753.7	97.0
0°-90°	777.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	777.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1211	
5°	1169	107
15°	845	233
25°	460	212
35°	201	128
45°	63	51
55°	25	23
65°	13	14
75°	7	7
85°	2	2
90°	0	



TEST NUMBER: P1300347

CATALOG NUMBER: P3AS17R30W2N902765DE010 E3DL1WH_6500K

CANDELA DISTRIBUTION (FULL):

0°	
0°	1210.8
1°	1209.6
2°	1204.8
3°	1196.4
4°	1184.3
5°	1168.7
6°	1149.4
7°	1128.9
8°	1102.4
9°	1072.3
10°	1041.0
11°	1004.8
12°	966.3
13°	927.7
14°	885.5
15°	844.6
17.5°	737.4
20°	636.1
22.5°	542.2
25°	460.2
27.5°	385.5
30°	319.3
32.5°	257.8
35°	201.2
37.5°	154.2
40°	115.7
42.5°	84.3
45°	62.7
47.5°	47.0
50°	34.9
52.5°	27.7
55°	25.3
57.5°	21.7
60°	19.3
62.5°	15.7
65°	13.3
67.5°	12.0
70°	9.6
72.5°	8.4
75°	7.2
77.5°	6.0
80°	3.6
82.5°	2.4
85°	2.4
87.5°	1.2



TEST NUMBER: P1300347

CATALOG NUMBER: P3AS17R30W2N902765DE010 E3DL1WH_6500K

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)