

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1300392

Luminaire Tested: P3AS17R30W2N902765DE010 E3DLP1GPH\_3500K

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1300392  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-13)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS17R30W2N902765DE010 E3DLP1GPH\_3500K  
Description: 3in Adjustable Tunable White LED luminaire with, R30 optic, 3500K CCT AND, 90CRI ,  
E3DLP1GPH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 383.1 lumens  
Efficiency: N/A  
Efficacy: 19.7 lumens/watt  
Spacing Criteria (0/90/45): 0.66 / 0.66 / 0.7  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 19.4  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1300392  
CATALOG NUMBER: P3AS17R30W2N902765DE010 E3DLP1GPH\_3500K

### Luminous Intensity Polar Plot







TEST NUMBER: P1300392

CATALOG NUMBER: P3AS17R30W2N902765DE010 E3DLP1GPH\_3500K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	53.0	13.8
10°-20°	114.7	29.9
20°-30°	104.3	27.2
30°-40°	63.1	16.5
40°-50°	25.3	6.6
50°-60°	11.2	2.9
60°-70°	6.7	1.8
70°-80°	3.7	1.0
80°-90°	1.1	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	272.0	71.0
0°-40°	335.0	87.5
0°-60°	371.5	97.0
0°-90°	383.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	383.1	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	597	
5°	576	53
15°	416	115
25°	227	104
35°	99	63
45°	31	25
55°	12	11
65°	6	7
75°	4	4
85°	1	1
90°	0	



TEST NUMBER: P1300392  
CATALOG NUMBER: P3AS17R30W2N902765DE010 E3DLP1GPH\_3500K

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	596.9
1°	596.3
2°	593.9
3°	589.7
4°	583.8
5°	576.1
6°	566.6
7°	556.5
8°	543.4
9°	528.6
10°	513.1
11°	495.3
12°	476.3
13°	457.3
14°	436.5
15°	416.3
17.5°	363.5
20°	313.6
22.5°	267.2
25°	226.9
27.5°	190.0
30°	157.4
32.5°	127.1
35°	99.2
37.5°	76.0
40°	57.0
42.5°	41.6
45°	30.9
47.5°	23.2
50°	17.2
52.5°	13.7
55°	12.5
57.5°	10.7
60°	9.5
62.5°	7.7
65°	6.5
67.5°	5.9
70°	4.8
72.5°	4.2
75°	3.6
77.5°	3.0
80°	1.8
82.5°	1.2
85°	1.2
87.5°	0.6



TEST NUMBER: P1300392  
CATALOG NUMBER: P3AS17R30W2N902765DE010 E3DLP1GPH\_3500K

CANDELA DISTRIBUTION (continued):

0°  
90° | 0.0

(END OF REPORT)