

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1297959

Luminaire Tested: P3AS13R55W2N902750DE010 E3DLD1GPH_5000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1297959
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-34)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R55W2N902750DE010 E3DLD1GPH_5000K
Description: 3in Adjustable Tunable White LED luminaire with, R55 optic, 5000K CCT AND, 90CRI ,
E3DLD1GPH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 320.0 lumens
Efficiency: N/A
Efficacy: 26.0 lumens/watt
Spacing Criteria (0/90/45): 0.91 / 0.91 / 0.97
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 12.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1297959
CATALOG NUMBER: P3AS13R55W2N902750DE010 E3DLD1GPH_5000K

Luminous Intensity Polar Plot





TEST NUMBER: P1297959

CATALOG NUMBER: P3AS13R55W2N902750DE010 E3DLD1GPH_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	25.3	7.9
10°-20°	65.7	20.5
20°-30°	82.3	25.7
30°-40°	73.4	22.9
40°-50°	43.0	13.4
50°-60°	14.9	4.6
60°-70°	9.0	2.8
70°-80°	5.0	1.6
80°-90°	1.4	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	173.3	54.2
0°-40°	246.7	77.1
0°-60°	304.6	95.2
0°-90°	320.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	320.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	274	
5°	270	25
15°	235	66
25°	180	82
35°	118	73
45°	54	43
55°	14	15
65°	9	9
75°	4	5
85°	1	1
90°	0	



TEST NUMBER: P1297959
CATALOG NUMBER: P3AS13R55W2N902750DE010 E3DLD1GPH_5000K

CANDELA DISTRIBUTION (FULL):

	0°
0°	274.4
2.5°	272.9
5°	269.9
7.5°	263.8
10°	256.2
12.5°	246.8
15°	235.1
17.5°	222.6
20°	208.6
22.5°	194.3
25°	179.5
27.5°	164.8
30°	150.0
32.5°	134.2
35°	117.9
37.5°	102.0
40°	86.9
42.5°	70.7
45°	54.4
47.5°	41.6
50°	30.2
52.5°	19.7
55°	14.0
57.5°	12.5
60°	11.3
62.5°	10.2
65°	9.1
67.5°	7.9
70°	6.8
72.5°	5.7
75°	4.5
77.5°	3.8
80°	3.0
82.5°	1.9
85°	1.1
87.5°	0.8
90°	0.0

(END OF REPORT)