

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1297981

Luminaire Tested: P3AS13R55W2N902750DE010 E3DLD1WMH\_3000K

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1297981  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-34)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS13R55W2N902750DE010 E3DLD1WMH\_3000K  
Description: 3in Adjustable Tunable White LED luminaire with, R55 optic, 3000K CCT AND, 90CRI ,  
E3DLD1WMH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 647.0 lumens  
Efficiency: N/A  
Efficacy: 52.6 lumens/watt  
Spacing Criteria (0/90/45): 0.91 / 0.91 / 0.97  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 12.3  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1297981  
CATALOG NUMBER: P3AS13R55W2N902750DE010 E3DLD1WMH\_3000K

### Luminous Intensity Polar Plot





TEST NUMBER: P1297981

CATALOG NUMBER: P3AS13R55W2N902750DE010 E3DLD1WMH\_3000K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	112	109	106	103	110	107	104	102	103	100	98	99	97	96	95	94	93	91
2	105	100	95	91	103	98	93	90	94	91	88	91	88	86	89	86	84	82
3	99	91	85	81	97	90	84	80	87	82	79	85	81	77	82	79	76	74
4	93	84	77	72	91	83	77	72	80	75	71	78	74	70	76	73	69	68
5	87	77	71	66	85	76	70	65	75	69	65	73	68	64	71	67	64	62
6	82	72	65	60	80	71	64	60	69	64	59	68	63	59	66	62	58	57
7	77	67	60	55	76	66	59	55	65	59	54	63	58	54	62	57	54	52
8	73	62	55	51	72	62	55	51	60	55	50	59	54	50	58	53	50	48
9	69	58	51	47	68	58	51	47	57	51	47	56	50	46	55	50	46	45
10	65	55	48	44	64	54	48	44	53	47	43	52	47	43	52	47	43	42

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	121657
5°	120097
10°	115362
15°	107901
20°	98429
25°	87828
30°	76822
35°	63818
40°	50323
45°	34112
50°	20844
55°	10819
60°	10043
65°	9495
70°	8848
75°	7795
80°	7703
85°	5787

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 34112 cd/sqm



TEST NUMBER: P1297981

CATALOG NUMBER: P3AS13R55W2N902750DE010 E3DLD1WMH\_3000K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	51.2	7.9
10°-20°	132.8	20.5
20°-30°	166.4	25.7
30°-40°	148.5	23.0
40°-50°	87.0	13.4
50°-60°	30.0	4.6
60°-70°	18.1	2.8
70°-80°	10.1	1.6
80°-90°	2.9	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	350.4	54.2
0°-40°	498.9	77.1
0°-60°	615.9	95.2
0°-90°	647.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	647.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	555	
5°	546	51
15°	475	133
25°	363	166
35°	238	149
45°	110	87
55°	28	30
65°	18	18
75°	9	10
85°	2	3
90°	0	



TEST NUMBER: P1297981  
CATALOG NUMBER: P3AS13R55W2N902750DE010 E3DLD1WMH\_3000K

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	554.8
2.5°	551.7
5°	545.6
7.5°	533.4
10°	518.1
12.5°	499.0
15°	475.3
17.5°	450.1
20°	421.8
22.5°	392.8
25°	363.0
27.5°	333.2
30°	303.4
32.5°	271.3
35°	238.4
37.5°	206.3
40°	175.8
42.5°	142.9
45°	110.0
47.5°	84.1
50°	61.1
52.5°	39.7
55°	28.3
57.5°	25.2
60°	22.9
62.5°	20.6
65°	18.3
67.5°	16.0
70°	13.8
72.5°	11.5
75°	9.2
77.5°	7.6
80°	6.1
82.5°	3.8
85°	2.3
87.5°	1.5
90°	0.0

(END OF REPORT)