

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1300444

Luminaire Tested: P3AS17R35W2N902750DE010 E3CB1MB_2700K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1300444
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-20)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R35W2N902750DE010 E3CB1MB_2700K
Description: 3in Adjustable Tunable White LED luminaire with, R35 optic, 2700K CCT AND, 90CRI ,
E3CB1MB TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1375.0 lumens
Efficiency: N/A
Efficacy: 70.9 lumens/watt
Spacing Criteria (0/90/45): 0.58 / 0.58 / 0.52
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 19.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1300444
CATALOG NUMBER: P3AS17R35W2N902750DE010 E3CB1MB_2700K

Luminous Intensity Polar Plot





TEST NUMBER: P1300444

CATALOG NUMBER: P3AS17R35W2N902750DE010 E3CB1MB_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	115	113	111	109	112	110	109	107	106	105	104	103	102	101	99	99	98	96			96
2	111	107	104	101	109	105	103	100	102	100	98	99	98	96	97	95	94	93			93
3	107	102	98	95	105	101	97	95	98	96	93	96	94	92	94	92	90	89			89
4	104	98	94	91	102	97	93	90	95	92	89	93	90	88	91	89	87	86			86
5	100	94	90	87	99	93	89	86	92	88	86	90	87	85	89	86	84	83			83
6	97	91	86	83	96	90	86	83	89	85	82	87	84	82	86	83	81	80			80
7	94	87	83	80	93	87	83	80	86	82	79	85	81	79	84	81	79	78			78
8	91	84	80	77	90	84	80	77	83	79	77	82	79	76	81	78	76	75			75
9	89	82	77	74	88	81	77	74	80	77	74	80	76	74	79	76	74	73			73
10	86	79	75	72	85	79	75	72	78	74	72	77	74	72	77	74	71	70			70

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	896595
5°	878316
10°	817108
15°	599073
20°	306767
25°	110571
30°	43045
35°	15071
40°	6212
45°	1675
50°	1467
55°	1644
60°	1403
65°	1141
70°	1410
75°	1864
80°	1389
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 75°
 Luminance: 1864 cd/sqm



TEST NUMBER: P1300444

CATALOG NUMBER: P3AS17R35W2N902750DE010 E3CB1MB_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	372.0	27.1
10°-20°	698.0	50.8
20°-30°	247.1	18.0
30°-40°	43.3	3.1
40°-50°	6.3	0.5
50°-60°	3.5	0.3
60°-70°	2.5	0.2
70°-80°	1.9	0.1
80°-90°	0.4	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1317.1	95.8
0°-40°	1360.3	98.9
0°-60°	1370.1	99.6
0°-90°	1375.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1375.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4089	
5°	3990	372
15°	2639	698
25°	457	247
35°	56	43
45°	5	6
55°	4	3
65°	2	3
75°	2	2
85°	0	0
90°	0	



TEST NUMBER: P1300444

CATALOG NUMBER: P3AS17R35W2N902750DE010 E3CB1MB_2700K

CANDELA DISTRIBUTION (FULL):

0°	
0°	4088.8
1°	4087.7
2°	4074.7
3°	4049.8
4°	4027.1
5°	3990.2
6°	3952.3
7°	3910.1
8°	3858.1
9°	3776.9
10°	3669.7
11°	3521.4
12°	3342.7
13°	3130.5
14°	2896.6
15°	2638.9
17.5°	1965.3
20°	1314.6
22.5°	792.6
25°	457.0
27.5°	272.9
30°	170.0
32.5°	98.5
35°	56.3
37.5°	35.7
40°	21.7
42.5°	10.8
45°	5.4
47.5°	4.3
50°	4.3
52.5°	4.3
55°	4.3
57.5°	3.2
60°	3.2
62.5°	3.2
65°	2.2
67.5°	2.2
70°	2.2
72.5°	2.2
75°	2.2
77.5°	1.1
80°	1.1
82.5°	1.1
85°	0.0
87.5°	0.0



TEST NUMBER: P1300444

CATALOG NUMBER: P3AS17R35W2N902750DE010 E3CB1MB_2700K

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)