

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1298025

Luminaire Tested: P3AS13R55W2N902765DE010 E3CB1MMS_5000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1298025
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-36)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R55W2N902765DE010 E3CB1MMS_5000K
Description: 3in Adjustable Tunable White LED luminaire with, R55 optic, 5000K CCT AND, 90CRI ,
E3CB1MMS TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1026.9 lumens
Efficiency: N/A
Efficacy: 83.5 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.82
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 12.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1298025
CATALOG NUMBER: P3AS13R55W2N902765DE010 E3CB1MMS_5000K

Luminous Intensity Polar Plot





TEST NUMBER: P1298025
 CATALOG NUMBER: P3AS13R55W2N902765DE010 E3CB1MMS_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	114	111	109	107	112	109	107	105	105	104	102	101	100	99	98	97	96	94	94	94	94
2	109	104	101	98	107	103	99	96	100	97	94	97	94	92	94	92	90	89	89	89	89
3	104	98	94	90	102	97	93	89	94	91	88	92	89	86	90	87	85	84	84	84	84
4	99	92	87	84	98	91	87	83	89	85	82	87	84	81	86	83	80	79	79	79	79
5	95	87	82	78	93	86	81	78	85	80	77	83	79	76	82	78	76	74	74	74	74
6	91	83	77	73	89	82	77	73	80	76	72	79	75	72	78	74	72	70	70	70	70
7	87	78	73	69	85	78	72	69	76	72	68	75	71	68	74	70	68	66	66	66	66
8	83	74	69	65	82	74	69	65	73	68	65	72	67	64	71	67	64	63	63	63	63
9	79	71	65	61	78	70	65	61	69	64	61	68	64	61	68	64	61	60	60	60	60
10	76	67	62	58	75	67	62	58	66	61	58	65	61	58	65	61	58	57	57	57	57

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	284846
5°	282192
10°	293537
15°	289468
20°	266933
25°	217174
30°	131919
35°	45668
40°	13024
45°	6233
50°	2627
55°	1185
60°	1360
65°	1193
70°	962
75°	1271
80°	1010
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 6233 cd/sqm



TEST NUMBER: P1298025
 CATALOG NUMBER: P3AS13R55W2N902765DE010 E3CB1MMS_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	123.9	12.1
10°-20°	354.4	34.5
20°-30°	395.1	38.5
30°-40°	129.2	12.6
40°-50°	17.0	1.7
50°-60°	3.6	0.4
60°-70°	2.1	0.2
70°-80°	1.3	0.1
80°-90°	0.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	873.4	85.0
0°-40°	1002.6	97.6
0°-60°	1023.2	99.6
0°-90°	1026.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1026.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1299	
5°	1282	124
15°	1275	354
25°	898	395
35°	171	129
45°	20	17
55°	3	4
65°	2	2
75°	2	1
85°	0	0
90°	0	



TEST NUMBER: P1298025
CATALOG NUMBER: P3AS13R55W2N902765DE010 E3CB1MMS_5000K

CANDELA DISTRIBUTION (FULL):

	0°
0°	1299.0
2.5°	1289.7
5°	1282.0
7.5°	1300.5
10°	1318.3
12.5°	1309.0
15°	1275.1
17.5°	1221.0
20°	1143.9
22.5°	1037.3
25°	897.6
27.5°	720.1
30°	521.0
32.5°	319.5
35°	170.6
37.5°	86.4
40°	45.5
42.5°	29.3
45°	20.1
47.5°	13.9
50°	7.7
52.5°	4.6
55°	3.1
57.5°	3.1
60°	3.1
62.5°	2.3
65°	2.3
67.5°	1.5
70°	1.5
72.5°	1.5
75°	1.5
77.5°	0.8
80°	0.8
82.5°	0.8
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)