

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1300559

Luminaire Tested: P3AS17R35W2N902750DE010 E3DLP1WH\_2700K

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1300559  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-19)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS17R35W2N902750DE010 E3DLP1WH\_2700K  
Description: 3in Adjustable Tunable White LED luminaire with, R35 optic, 2700K CCT AND, 90CRI ,  
E3DLP1WH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1138.0 lumens  
Efficiency: N/A  
Efficacy: 58.7 lumens/watt  
Spacing Criteria (0/90/45): 0.58 / 0.58 / 0.58  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 19.4  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1300559  
CATALOG NUMBER: P3AS17R35W2N902750DE010 E3DLP1WH\_2700K

### Luminous Intensity Polar Plot







TEST NUMBER: P1300559

CATALOG NUMBER: P3AS17R35W2N902750DE010 E3DLP1WH\_2700K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	228.0	20.0
10°-20°	441.8	38.8
20°-30°	289.3	25.4
30°-40°	117.4	10.3
40°-50°	35.2	3.1
50°-60°	12.0	1.1
60°-70°	8.0	0.7
70°-80°	4.7	0.4
80°-90°	1.6	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	959.1	84.3
0°-40°	1076.5	94.6
0°-60°	1123.6	98.7
0°-90°	1138.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1138.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	2618	
5°	2506	228
15°	1622	442
25°	616	289
35°	179	117
45°	42	35
55°	13	12
65°	8	8
75°	4	5
85°	1	2
90°	0	



TEST NUMBER: P1300559  
CATALOG NUMBER: P3AS17R35W2N902750DE010 E3DLP1WH\_2700K

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	2617.5
1°	2613.1
2°	2601.2
3°	2577.4
4°	2549.3
5°	2506.0
6°	2451.8
7°	2391.2
8°	2323.0
9°	2245.1
10°	2158.5
11°	2062.1
12°	1961.5
13°	1848.9
14°	1741.7
15°	1621.6
17.5°	1330.4
20°	1055.4
22.5°	811.9
25°	615.9
27.5°	459.0
30°	337.7
32.5°	247.9
35°	178.6
37.5°	126.7
40°	88.8
42.5°	61.7
45°	42.2
47.5°	28.1
50°	18.4
52.5°	14.1
55°	13.0
57.5°	11.9
60°	10.8
62.5°	9.7
65°	7.6
67.5°	6.5
70°	6.5
72.5°	5.4
75°	4.3
77.5°	3.2
80°	3.2
82.5°	2.2
85°	1.1
87.5°	1.1



TEST NUMBER: P1300559  
CATALOG NUMBER: P3AS17R35W2N902750DE010 E3DLP1WH\_2700K

CANDELA DISTRIBUTION (continued):



(END OF REPORT)