

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1298122

Luminaire Tested: P3AS13R55W2N902765DE010 E3DLD1GPH\_6500K

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1298122  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-34)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS13R55W2N902765DE010 E3DLD1GPH\_6500K  
Description: 3in Adjustable Tunable White LED luminaire with, R55 optic, 6500K CCT AND, 90CRI ,  
E3DLD1GPH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 320.0 lumens  
Efficiency: N/A  
Efficacy: 26.0 lumens/watt  
Spacing Criteria (0/90/45): 0.91 / 0.91 / 0.97  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 12.3  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1298122  
CATALOG NUMBER: P3AS13R55W2N902765DE010 E3DLD1GPH\_6500K

### Luminous Intensity Polar Plot





TEST NUMBER: P1298122  
 CATALOG NUMBER: P3AS13R55W2N902765DE010 E3DLD1GPH\_6500K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	112	109	106	103	110	107	104	102	103	100	98	99	97	95	95	94	93	91
2	105	100	95	91	103	98	93	90	94	91	88	91	88	86	89	86	84	82
3	99	91	85	81	97	90	84	80	87	82	79	85	81	77	82	79	76	74
4	93	84	77	72	91	83	77	72	80	75	71	78	74	70	76	73	69	68
5	87	77	71	66	85	76	70	65	75	69	65	73	68	64	71	67	64	62
6	82	72	65	60	80	71	64	60	69	64	59	68	63	59	66	62	58	57
7	77	67	60	55	76	66	59	55	65	59	54	63	58	54	62	57	54	52
8	73	62	55	51	72	62	55	51	60	55	50	59	54	50	58	53	50	48
9	69	58	51	47	68	58	51	47	57	51	47	56	50	46	55	50	46	45
10	65	55	48	44	64	54	48	44	53	47	43	52	47	43	52	47	43	42

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	60171
5°	59410
10°	57046
15°	53371
20°	48678
25°	43430
30°	37981
35°	31561
40°	24875
45°	16870
50°	10302
55°	5352
60°	4956
65°	4722
70°	4360
75°	3813
80°	3788
85°	2768

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 16870 cd/sqm



TEST NUMBER: P1298122

CATALOG NUMBER: P3AS13R55W2N902765DE010 E3DLD1GPH\_6500K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	25.3	7.9
10°-20°	65.7	20.5
20°-30°	82.3	25.7
30°-40°	73.4	22.9
40°-50°	43.0	13.4
50°-60°	14.9	4.6
60°-70°	9.0	2.8
70°-80°	5.0	1.6
80°-90°	1.4	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	173.3	54.2
0°-40°	246.7	77.1
0°-60°	304.6	95.2
0°-90°	320.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	320.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	274	
5°	270	25
15°	235	66
25°	180	82
35°	118	73
45°	54	43
55°	14	15
65°	9	9
75°	4	5
85°	1	1
90°	0	



TEST NUMBER: P1298122  
CATALOG NUMBER: P3AS13R55W2N902765DE010 E3DLD1GPH\_6500K

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	274.4
2.5°	272.9
5°	269.9
7.5°	263.8
10°	256.2
12.5°	246.8
15°	235.1
17.5°	222.6
20°	208.6
22.5°	194.3
25°	179.5
27.5°	164.8
30°	150.0
32.5°	134.2
35°	117.9
37.5°	102.0
40°	86.9
42.5°	70.7
45°	54.4
47.5°	41.6
50°	30.2
52.5°	19.7
55°	14.0
57.5°	12.5
60°	11.3
62.5°	10.2
65°	9.1
67.5°	7.9
70°	6.8
72.5°	5.7
75°	4.5
77.5°	3.8
80°	3.0
82.5°	1.9
85°	1.1
87.5°	0.8
90°	0.0

(END OF REPORT)