

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1300605

Luminaire Tested: P3AS17R35W2N902765DE010 E3CD1MB_4000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1300605
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-20)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R35W2N902765DE010 E3CD1MB_4000K
Description: 3in Adjustable Tunable White LED luminaire with, R35 optic, 4000K CCT AND, 90CRI ,
E3CD1MB TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1538.9 lumens
Efficiency: N/A
Efficacy: 79.3 lumens/watt
Spacing Criteria (0/90/45): 0.58 / 0.58 / 0.52
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 19.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1300605
CATALOG NUMBER: P3AS17R35W2N902765DE010 E3CD1MB_4000K

Luminous Intensity Polar Plot





TEST NUMBER: P1300605

CATALOG NUMBER: P3AS17R35W2N902765DE010 E3CD1MB_4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

| | | | | | | | | | | | | | | | | | | | | | |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|
| RF | 20 | | | | 20 | | | | 20 | | | | 20 | | | | 20 | | | | |
| RC | 80 | | | | 70 | | | | 50 | | | | 30 | | | | 10 | | | 0 | |
| RW | 70 | 50 | 30 | 10 | 70 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 0 |
| RCR | | | | | | | | | | | | | | | | | | | | | |
| 0 | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 102 | 102 | 102 | 100 |
| 1 | 115 | 113 | 111 | 109 | 112 | 110 | 109 | 107 | 106 | 105 | 104 | 103 | 102 | 101 | 99 | 99 | 98 | 98 | 98 | 98 | 96 |
| 2 | 111 | 107 | 104 | 101 | 109 | 105 | 103 | 100 | 102 | 100 | 98 | 99 | 98 | 96 | 97 | 95 | 94 | 94 | 94 | 94 | 93 |
| 3 | 107 | 102 | 98 | 95 | 105 | 101 | 98 | 95 | 98 | 96 | 93 | 96 | 94 | 92 | 94 | 92 | 90 | 94 | 92 | 90 | 89 |
| 4 | 104 | 98 | 94 | 91 | 102 | 97 | 93 | 90 | 95 | 92 | 89 | 93 | 90 | 88 | 91 | 89 | 87 | 91 | 89 | 87 | 86 |
| 5 | 100 | 94 | 90 | 87 | 99 | 93 | 89 | 86 | 92 | 88 | 86 | 90 | 87 | 85 | 89 | 86 | 84 | 89 | 86 | 84 | 83 |
| 6 | 97 | 91 | 86 | 83 | 96 | 90 | 86 | 83 | 89 | 85 | 82 | 87 | 84 | 82 | 86 | 83 | 81 | 86 | 83 | 81 | 80 |
| 7 | 94 | 87 | 83 | 80 | 93 | 87 | 83 | 80 | 86 | 82 | 79 | 85 | 81 | 79 | 84 | 81 | 79 | 84 | 81 | 79 | 78 |
| 8 | 91 | 84 | 80 | 77 | 90 | 84 | 80 | 77 | 83 | 79 | 77 | 82 | 79 | 76 | 81 | 78 | 76 | 81 | 78 | 76 | 75 |
| 9 | 89 | 82 | 77 | 74 | 88 | 81 | 77 | 74 | 80 | 77 | 74 | 80 | 76 | 74 | 79 | 76 | 74 | 79 | 76 | 74 | 73 |
| 10 | 86 | 79 | 75 | 72 | 85 | 79 | 75 | 72 | 78 | 74 | 72 | 77 | 74 | 72 | 77 | 74 | 71 | 77 | 74 | 71 | 70 |

AVERAGE LUMINANCE (cd/sqm):

| | |
|-----|---------|
| | 0° |
| 0° | 1003538 |
| 5° | 983092 |
| 10° | 914568 |
| 15° | 670515 |
| 20° | 343357 |
| 25° | 123757 |
| 30° | 48185 |
| 35° | 16865 |
| 40° | 6927 |
| 45° | 1892 |
| 50° | 1637 |
| 55° | 1835 |
| 60° | 1579 |
| 65° | 1245 |
| 70° | 1539 |
| 75° | 2033 |
| 80° | 1515 |
| 85° | 0 |

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 75°
 Luminance: 2033 cd/sqm



TEST NUMBER: P1300605

CATALOG NUMBER: P3AS17R35W2N902765DE010 E3CD1MB_4000K

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10° | 416.4 | 27.1 |
| 10°-20° | 781.2 | 50.8 |
| 20°-30° | 276.6 | 18.0 |
| 30°-40° | 48.4 | 3.1 |
| 40°-50° | 7.1 | 0.5 |
| 50°-60° | 3.9 | 0.3 |
| 60°-70° | 2.8 | 0.2 |
| 70°-80° | 2.1 | 0.1 |
| 80°-90° | 0.5 | 0.0 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-30° | 1474.2 | 95.8 |
| 0°-40° | 1522.6 | 98.9 |
| 0°-60° | 1533.5 | 99.7 |
| 0°-90° | 1538.9 | 100.0 |
| 90°-120° | 0.0 | 0.0 |
| 90°-150° | 0.0 | 0.0 |
| 90°-180° | 0.0 | 0.0 |
| 0°-180° | 1538.9 | 100.0 |

CANDELA DISTRIBUTION:

| | 0° | Flux |
|-----|------|------|
| 0° | 4576 | |
| 5° | 4466 | 416 |
| 15° | 2954 | 781 |
| 25° | 512 | 277 |
| 35° | 63 | 48 |
| 45° | 6 | 7 |
| 55° | 5 | 4 |
| 65° | 2 | 3 |
| 75° | 2 | 2 |
| 85° | 0 | 0 |
| 90° | 0 | |



TEST NUMBER: P1300605

CATALOG NUMBER: P3AS17R35W2N902765DE010 E3CD1MB_4000K

CANDELA DISTRIBUTION (FULL):

| 0° | |
|-------|--------|
| 0° | 4576.5 |
| 1° | 4575.2 |
| 2° | 4560.7 |
| 3° | 4532.8 |
| 4° | 4507.4 |
| 5° | 4466.2 |
| 6° | 4423.8 |
| 7° | 4376.5 |
| 8° | 4318.3 |
| 9° | 4227.4 |
| 10° | 4107.4 |
| 11° | 3941.4 |
| 12° | 3741.4 |
| 13° | 3503.9 |
| 14° | 3242.1 |
| 15° | 2953.6 |
| 17.5° | 2199.8 |
| 20° | 1471.4 |
| 22.5° | 887.2 |
| 25° | 511.5 |
| 27.5° | 305.4 |
| 30° | 190.3 |
| 32.5° | 110.3 |
| 35° | 63.0 |
| 37.5° | 40.0 |
| 40° | 24.2 |
| 42.5° | 12.1 |
| 45° | 6.1 |
| 47.5° | 4.8 |
| 50° | 4.8 |
| 52.5° | 4.8 |
| 55° | 4.8 |
| 57.5° | 3.6 |
| 60° | 3.6 |
| 62.5° | 3.6 |
| 65° | 2.4 |
| 67.5° | 2.4 |
| 70° | 2.4 |
| 72.5° | 2.4 |
| 75° | 2.4 |
| 77.5° | 1.2 |
| 80° | 1.2 |
| 82.5° | 1.2 |
| 85° | 0.0 |
| 87.5° | 0.0 |



TEST NUMBER: P1300605
CATALOG NUMBER: P3AS17R35W2N902765DE010 E3CD1MB_4000K

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)