

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1300627

Luminaire Tested: P3AS17R35W2N902765DE010 E3DL1GPH_3000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1300627
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-19)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R35W2N902765DE010 E3DL1GPH_3000K
Description: 3in Adjustable Tunable White LED luminaire with, R35 optic, 3000K CCT AND, 90CRI ,
E3DL1GPH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 615.0 lumens
Efficiency: N/A
Efficacy: 31.7 lumens/watt
Spacing Criteria (0/90/45): 0.58 / 0.58 / 0.58
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 19.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1300627
CATALOG NUMBER: P3AS17R35W2N902765DE010 E3DL1GPH_3000K

Luminous Intensity Polar Plot





TEST NUMBER: P1300627

CATALOG NUMBER: P3AS17R35W2N902765DE010 E3DL1GPH_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	102	102	102	100
1	114	112	109	107	112	109	107	106	105	104	102	102	100	99	98	97	96	96	96	96	95
2	109	105	101	98	107	103	100	97	100	97	95	97	95	93	94	93	91	91	91	91	90
3	105	99	95	91	103	98	94	90	95	92	89	93	90	88	91	88	86	86	86	86	85
4	100	94	89	85	99	93	88	85	91	87	84	89	85	83	87	84	82	82	82	82	80
5	96	89	84	80	95	88	83	80	86	82	79	85	81	78	83	80	78	78	78	78	76
6	92	85	80	76	91	84	79	76	83	78	75	81	77	75	80	77	74	74	74	74	73
7	89	81	76	72	88	80	75	72	79	75	71	78	74	71	77	73	71	71	71	71	70
8	85	77	72	69	84	77	72	68	76	71	68	75	71	68	74	70	68	68	68	68	66
9	82	74	69	66	81	74	69	65	73	68	65	72	68	65	71	68	65	65	65	65	64
10	79	71	66	63	78	71	66	63	70	66	63	69	65	62	69	65	62	62	62	62	61

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	310173
5°	298106
10°	259737
15°	198934
20°	133105
25°	80545
30°	46210
35°	25832
40°	13740
45°	7071
50°	3377
55°	2676
60°	2588
65°	2127
70°	2244
75°	1949
80°	2273
85°	1510

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 7071 cd/sqm



TEST NUMBER: P1300627

CATALOG NUMBER: P3AS17R35W2N902765DE010 E3DL1GPH_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	123.2	20.0
10°-20°	238.8	38.8
20°-30°	156.3	25.4
30°-40°	63.4	10.3
40°-50°	19.0	3.1
50°-60°	6.5	1.0
60°-70°	4.3	0.7
70°-80°	2.5	0.4
80°-90°	0.9	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	518.3	84.3
0°-40°	581.7	94.6
0°-60°	607.2	98.7
0°-90°	615.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	615.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1414	
5°	1354	123
15°	876	239
25°	333	156
35°	96	63
45°	23	19
55°	7	6
65°	4	4
75°	2	3
85°	1	1
90°	0	



TEST NUMBER: P1300627
CATALOG NUMBER: P3AS17R35W2N902765DE010 E3DL1GPH_3000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	1414.5
1°	1412.2
2°	1405.8
3°	1392.9
4°	1377.7
5°	1354.3
6°	1325.0
7°	1292.3
8°	1255.4
9°	1213.3
10°	1166.5
11°	1114.4
12°	1060.0
13°	999.2
14°	941.3
15°	876.3
17.5°	719.0
20°	570.4
22.5°	438.8
25°	332.9
27.5°	248.0
30°	182.5
32.5°	134.0
35°	96.5
37.5°	68.4
40°	48.0
42.5°	33.3
45°	22.8
47.5°	15.2
50°	9.9
52.5°	7.6
55°	7.0
57.5°	6.4
60°	5.9
62.5°	5.3
65°	4.1
67.5°	3.5
70°	3.5
72.5°	2.9
75°	2.3
77.5°	1.8
80°	1.8
82.5°	1.2
85°	0.6
87.5°	0.6



TEST NUMBER: P1300627
CATALOG NUMBER: P3AS17R35W2N902765DE010 E3DL1GPH_3000K

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)