

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1300630

Luminaire Tested: P3AS17R35W2N902765DE010 E3DL1GPH\_5000K

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1300630  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-19)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS17R35W2N902765DE010 E3DL1GPH\_5000K  
Description: 3in Adjustable Tunable White LED luminaire with, R35 optic, 5000K CCT AND, 90CRI ,  
E3DL1GPH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 621.0 lumens  
Efficiency: N/A  
Efficacy: 32.0 lumens/watt  
Spacing Criteria (0/90/45): 0.58 / 0.58 / 0.58  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 19.4  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1300630  
CATALOG NUMBER: P3AS17R35W2N902765DE010 E3DL1GPH\_5000K

### Luminous Intensity Polar Plot





TEST NUMBER: P1300630

CATALOG NUMBER: P3AS17R35W2N902765DE010 E3DL1GPH\_5000K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	102	102	102	100
1	114	112	109	107	112	109	107	106	105	104	102	102	100	99	98	97	96	96	96	96	95
2	109	105	101	98	107	103	100	97	100	97	95	97	95	93	94	93	91	91	91	91	90
3	105	99	95	91	103	98	94	90	95	92	89	93	90	88	91	88	86	86	86	86	85
4	100	94	89	85	99	93	88	85	91	87	84	89	85	83	87	84	82	82	82	82	80
5	96	89	84	80	95	88	83	80	86	82	79	85	81	78	83	80	78	78	78	78	76
6	92	85	80	76	91	84	79	76	83	78	75	81	77	75	80	77	74	74	74	74	73
7	89	81	76	72	88	80	75	72	79	75	71	78	74	71	77	73	71	71	71	71	70
8	85	77	72	69	84	77	72	68	76	71	68	75	71	68	74	70	68	68	68	68	66
9	82	74	69	66	81	74	69	65	73	68	65	72	68	65	71	68	65	65	65	65	64
10	79	71	66	63	78	71	66	63	70	66	63	69	65	62	69	65	62	62	62	62	61

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	313199
5°	301012
10°	262275
15°	200887
20°	134388
25°	81319
30°	46665
35°	26100
40°	13855
45°	7133
50°	3411
55°	2714
60°	2588
65°	2127
70°	2244
75°	2033
80°	2273
85°	1510

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 7133 cd/sqm



TEST NUMBER: P1300630  
 CATALOG NUMBER: P3AS17R35W2N902765DE010 E3DL1GPH\_5000K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	124.4	20.0
10°-20°	241.1	38.8
20°-30°	157.9	25.4
30°-40°	64.0	10.3
40°-50°	19.2	3.1
50°-60°	6.5	1.1
60°-70°	4.3	0.7
70°-80°	2.6	0.4
80°-90°	0.9	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	523.4	84.3
0°-40°	587.4	94.6
0°-60°	613.2	98.7
0°-90°	621.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	621.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1428	
5°	1368	124
15°	885	241
25°	336	158
35°	98	64
45°	23	19
55°	7	7
65°	4	4
75°	2	3
85°	1	1
90°	0	



TEST NUMBER: P1300630  
CATALOG NUMBER: P3AS17R35W2N902765DE010 E3DL1GPH\_5000K

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	1428.3
1°	1426.0
2°	1419.5
3°	1406.5
4°	1391.1
5°	1367.5
6°	1338.0
7°	1304.9
8°	1267.7
9°	1225.1
10°	1177.9
11°	1125.3
12°	1070.4
13°	1008.9
14°	950.4
15°	884.9
17.5°	726.0
20°	575.9
22.5°	443.0
25°	336.1
27.5°	250.5
30°	184.3
32.5°	135.3
35°	97.5
37.5°	69.1
40°	48.4
42.5°	33.7
45°	23.0
47.5°	15.4
50°	10.0
52.5°	7.7
55°	7.1
57.5°	6.5
60°	5.9
62.5°	5.3
65°	4.1
67.5°	3.5
70°	3.5
72.5°	3.0
75°	2.4
77.5°	1.8
80°	1.8
82.5°	1.2
85°	0.6
87.5°	0.6



TEST NUMBER: P1300630  
CATALOG NUMBER: P3AS17R35W2N902765DE010 E3DL1GPH\_5000K

CANDELA DISTRIBUTION (continued):

0°  
90° | 0.0

(END OF REPORT)