

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1298222

Luminaire Tested: P3AS13R60W2N902750DE010 E3D1H_4000K

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1298222
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-15)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R60W2N902750DE010 E3D1H_4000K
Description: 3in Adjustable Tunable White LED luminaire with, R60 optic, 4000K CCT AND, 90CRI , E3D1H TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 930.0 lumens
Efficiency: N/A
Efficacy: 75.6 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.88
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 12.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1298222

CATALOG NUMBER: P3AS13R60W2N902750DE010 E3D1H_4000K

Luminous Intensity Polar Plot





TEST NUMBER: P1298222

CATALOG NUMBER: P3AS13R60W2N902750DE010 E3D1H_4000K

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10° | 98.7 | 10.6 |
| 10°-20° | 268.6 | 28.9 |
| 20°-30° | 336.5 | 36.2 |
| 30°-40° | 188.1 | 20.2 |
| 40°-50° | 35.7 | 3.8 |
| 50°-60° | 1.8 | 0.2 |
| 60°-70° | 0.4 | 0.0 |
| 70°-80° | 0.2 | 0.0 |
| 80°-90° | 0.0 | 0.0 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-30° | 703.8 | 75.7 |
| 0°-40° | 891.8 | 95.9 |
| 0°-60° | 929.4 | 99.9 |
| 0°-90° | 930.0 | 100.0 |
| 90°-120° | 0.0 | 0.0 |
| 90°-150° | 0.0 | 0.0 |
| 90°-180° | 0.0 | 0.0 |
| 0°-180° | 930.0 | 100.0 |

CANDELA DISTRIBUTION:

| | 0° | Flux |
|-----|------|------|
| 0° | 1111 | |
| 5° | 1045 | 99 |
| 15° | 964 | 269 |
| 25° | 752 | 336 |
| 35° | 300 | 188 |
| 45° | 42 | 36 |
| 55° | 1 | 2 |
| 65° | 0 | 0 |
| 75° | 0 | 0 |
| 85° | 0 | 0 |
| 90° | 0 | |



TEST NUMBER: P1298222

CATALOG NUMBER: P3AS13R60W2N902750DE010 E3D1H_4000K

CANDELA DISTRIBUTION (FULL):

| 0° | |
|-------|--------|
| 0° | 1111.2 |
| 1° | 1106.7 |
| 2° | 1092.2 |
| 3° | 1075.1 |
| 4° | 1059.1 |
| 5° | 1045.0 |
| 6° | 1034.4 |
| 7° | 1025.3 |
| 8° | 1018.4 |
| 9° | 1011.9 |
| 10° | 1006.2 |
| 11° | 1000.5 |
| 12° | 994.1 |
| 13° | 986.1 |
| 14° | 976.6 |
| 15° | 964.4 |
| 16° | 949.6 |
| 17° | 932.8 |
| 18° | 913.8 |
| 19° | 892.1 |
| 20° | 872.3 |
| 21° | 851.0 |
| 22° | 829.0 |
| 23° | 805.8 |
| 24° | 780.3 |
| 25° | 752.1 |
| 26° | 719.0 |
| 27° | 682.1 |
| 28° | 640.6 |
| 29° | 596.5 |
| 30° | 549.0 |
| 31° | 501.0 |
| 32° | 451.6 |
| 32.5° | 424.6 |
| 33° | 400.2 |
| 34° | 349.6 |
| 35° | 299.8 |
| 36° | 254.9 |
| 37° | 207.3 |
| 37.5° | 185.7 |
| 38° | 164.3 |
| 39° | 132.4 |
| 40° | 108.8 |
| 42.5° | 66.2 |
| 45° | 41.8 |



TEST NUMBER: P1298222

CATALOG NUMBER: P3AS13R60W2N902750DE010 E3D1H_4000K

CANDELA DISTRIBUTION (continued):

| | 0° |
|-------|------|
| 47.5° | 23.2 |
| 50° | 8.4 |
| 52.5° | 1.9 |
| 55° | 1.1 |
| 57.5° | 0.8 |
| 60° | 0.8 |
| 62.5° | 0.4 |
| 65° | 0.4 |
| 67.5° | 0.4 |
| 70° | 0.4 |
| 72.5° | 0.4 |
| 75° | 0.0 |
| 77.5° | 0.0 |
| 80° | 0.0 |
| 82.5° | 0.0 |
| 85° | 0.0 |
| 87.5° | 0.0 |
| 90° | 0.0 |

(END OF REPORT)