

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1300688

Luminaire Tested: P3AS17R35W2N902765DE010 E3DLD1WH\_3500K

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1300688  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-18)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS17R35W2N902765DE010 E3DLD1WH\_3500K  
Description: 3in Adjustable Tunable White LED luminaire with, R35 optic, 3500K CCT AND, 90CRI ,  
E3DLD1WH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 980.0 lumens  
Efficiency: N/A  
Efficacy: 50.5 lumens/watt  
Spacing Criteria (0/90/45): 0.8 / 0.8 / 0.87  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 19.4  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1300688  
CATALOG NUMBER: P3AS17R35W2N902765DE010 E3DLD1WH\_3500K

### Luminous Intensity Polar Plot







TEST NUMBER: P1300688

CATALOG NUMBER: P3AS17R35W2N902765DE010 E3DLD1WH\_3500K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	92.6	9.5
10°-20°	225.8	23.0
20°-30°	258.8	26.4
30°-40°	211.2	21.5
40°-50°	106.5	10.9
50°-60°	39.5	4.0
60°-70°	26.5	2.7
70°-80°	14.7	1.5
80°-90°	4.4	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	577.2	58.9
0°-40°	788.3	80.4
0°-60°	934.3	95.3
0°-90°	980.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	980.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1021	
5°	996	93
15°	811	226
25°	564	259
35°	340	211
45°	134	106
55°	41	40
65°	27	27
75°	13	15
85°	4	4
90°	0	



TEST NUMBER: P1300688

CATALOG NUMBER: P3AS17R35W2N902765DE010 E3DLD1WH\_3500K

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	1020.9
1°	1019.7
2°	1017.3
3°	1012.4
4°	1005.1
5°	995.5
6°	983.3
7°	971.2
8°	955.5
9°	939.8
10°	921.6
11°	902.2
12°	881.6
13°	858.6
14°	834.4
15°	811.4
17.5°	749.6
20°	686.6
22.5°	622.5
25°	564.3
27.5°	507.4
30°	451.7
32.5°	396.0
35°	340.3
37.5°	284.6
40°	230.1
42.5°	179.2
45°	134.4
47.5°	96.9
50°	66.6
52.5°	48.4
55°	41.2
57.5°	37.5
60°	33.9
62.5°	30.3
65°	26.6
67.5°	23.0
70°	20.6
72.5°	17.0
75°	13.3
77.5°	10.9
80°	8.5
82.5°	6.1
85°	3.6
87.5°	2.4



TEST NUMBER: P1300688  
CATALOG NUMBER: P3AS17R35W2N902765DE010 E3DLD1WH\_3500K

CANDELA DISTRIBUTION (continued):

0°  
90° | 0.0

(END OF REPORT)