

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1300691

Luminaire Tested: P3AS17R35W2N902765DE010 E3DLD1WH\_6500K

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1300691  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-18)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS17R35W2N902765DE010 E3DLD1WH\_6500K  
Description: 3in Adjustable Tunable White LED luminaire with, R35 optic, 6500K CCT AND, 90CRI ,  
E3DLD1WH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 975.0 lumens  
Efficiency: N/A  
Efficacy: 50.3 lumens/watt  
Spacing Criteria (0/90/45): 0.8 / 0.8 / 0.87  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 19.4  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1300691  
CATALOG NUMBER: P3AS17R35W2N902765DE010 E3DLD1WH\_6500K

### Luminous Intensity Polar Plot





TEST NUMBER: P1300691  
 CATALOG NUMBER: P3AS17R35W2N902765DE010 E3DLD1WH\_6500K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	112	109	106	104	110	107	104	102	103	101	99	99	98	96	96	94	93	91			
2	106	100	96	92	104	98	94	91	95	92	89	92	89	87	89	87	85	83			
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76			
4	94	85	79	74	92	84	78	74	82	77	73	80	75	72	78	74	71	69			
5	89	79	73	68	87	78	72	67	76	71	67	75	70	66	73	69	66	64			
6	84	74	67	62	82	73	67	62	71	66	61	70	65	61	68	64	61	59			
7	79	69	62	57	78	68	62	57	67	61	57	65	60	57	64	60	56	55			
8	75	64	58	53	74	64	57	53	63	57	53	62	56	53	61	56	52	51			
9	71	60	54	50	70	60	54	50	59	53	49	58	53	49	57	52	49	48			
10	67	57	51	46	66	56	50	46	56	50	46	55	50	46	54	49	46	45			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	222723
5°	218005
10°	204160
15°	183247
20°	159404
25°	135855
30°	113790
35°	90641
40°	65523
45°	41462
50°	22618
55°	15674
60°	14780
65°	13750
70°	13143
75°	11268
80°	10607
85°	9057

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 41462 cd/sqm



TEST NUMBER: P1300691

CATALOG NUMBER: P3AS17R35W2N902765DE010 E3DLD1WH\_6500K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	92.2	9.5
10°-20°	224.6	23.0
20°-30°	257.4	26.4
30°-40°	210.1	21.5
40°-50°	105.9	10.9
50°-60°	39.4	4.0
60°-70°	26.4	2.7
70°-80°	14.6	1.5
80°-90°	4.4	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	574.2	58.9
0°-40°	784.3	80.4
0°-60°	929.6	95.3
0°-90°	975.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	975.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1016	
5°	990	92
15°	807	225
25°	562	257
35°	339	210
45°	134	106
55°	41	39
65°	26	26
75°	13	15
85°	4	4
90°	0	



TEST NUMBER: P1300691  
CATALOG NUMBER: P3AS17R35W2N902765DE010 E3DLD1WH\_6500K

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	1015.7
1°	1014.5
2°	1012.1
3°	1007.2
4°	1000.0
5°	990.4
6°	978.3
7°	966.3
8°	950.6
9°	935.0
10°	916.9
11°	897.6
12°	877.1
13°	854.2
14°	830.1
15°	807.2
17.5°	745.8
20°	683.1
22.5°	619.3
25°	561.5
27.5°	504.8
30°	449.4
32.5°	394.0
35°	338.6
37.5°	283.1
40°	228.9
42.5°	178.3
45°	133.7
47.5°	96.4
50°	66.3
52.5°	48.2
55°	41.0
57.5°	37.4
60°	33.7
62.5°	30.1
65°	26.5
67.5°	22.9
70°	20.5
72.5°	16.9
75°	13.3
77.5°	10.8
80°	8.4
82.5°	6.0
85°	3.6
87.5°	2.4



TEST NUMBER: P1300691  
CATALOG NUMBER: P3AS17R35W2N902765DE010 E3DLD1WH\_6500K

CANDELA DISTRIBUTION (continued):

0°  
90° | 0.0

(END OF REPORT)