

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1300700

Luminaire Tested: P3AS17R35W2N902765DE010 E3DLP1GPH\_3500K

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1300700  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-17)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS17R35W2N902765DE010 E3DLP1GPH\_3500K  
Description: 3in Adjustable Tunable White LED luminaire with, R35 optic, 3500K CCT AND, 90CRI ,  
E3DLP1GPH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 385.0 lumens  
Efficiency: N/A  
Efficacy: 19.8 lumens/watt  
Spacing Criteria (0/90/45): 0.69 / 0.69 / 0.72  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 19.4  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1300700  
CATALOG NUMBER: P3AS17R35W2N902765DE010 E3DLP1GPH\_3500K

### Luminous Intensity Polar Plot







TEST NUMBER: P1300700

CATALOG NUMBER: P3AS17R35W2N902765DE010 E3DLP1GPH\_3500K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	50.7	13.2
10°-20°	113.7	29.5
20°-30°	106.4	27.6
30°-40°	65.1	16.9
40°-50°	25.7	6.7
50°-60°	11.3	2.9
60°-70°	7.0	1.8
70°-80°	3.8	1.0
80°-90°	1.3	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	270.8	70.3
0°-40°	335.9	87.3
0°-60°	372.9	96.9
0°-90°	385.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	385.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	564	
5°	548	51
15°	413	114
25°	232	106
35°	103	65
45°	31	26
55°	12	11
65°	7	7
75°	4	4
85°	1	1
90°	0	



TEST NUMBER: P1300700  
CATALOG NUMBER: P3AS17R35W2N902765DE010 E3DLP1GPH\_3500K

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	564.3
1°	564.9
2°	563.2
3°	559.6
4°	554.3
5°	548.3
6°	540.6
7°	531.7
8°	521.1
9°	509.2
10°	495.6
11°	481.4
12°	465.9
13°	449.3
14°	431.0
15°	412.6
17.5°	365.2
20°	317.7
22.5°	272.1
25°	231.8
27.5°	194.4
30°	161.2
32.5°	130.4
35°	103.1
37.5°	78.8
40°	59.3
42.5°	42.7
45°	31.4
47.5°	22.5
50°	17.2
52.5°	14.2
55°	12.4
57.5°	10.7
60°	9.5
62.5°	8.3
65°	7.1
67.5°	5.9
70°	4.7
72.5°	4.1
75°	3.6
77.5°	3.0
80°	2.4
82.5°	1.8
85°	1.2
87.5°	0.6



TEST NUMBER: P1300700  
CATALOG NUMBER: P3AS17R35W2N902765DE010 E3DLP1GPH\_3500K

CANDELA DISTRIBUTION (continued):

0°  
90° | 0.0

(END OF REPORT)